

Temperature, Humidity, Digital Contact Sensor for Guardian

KATALOGNUMMER

21070-120



External sensor monitoring temperature, humidity and digital inputs with 2 RJ45 connectors. Up to 16 sensors can be daisy chained over patch cables and connected to one Guardian Management Port.

DESIGN

External sensor for the Guardian Management Gateway

A port is capable of monitoring up to 16 sensor devices with a total cable length of 40 meters

If an nVent SCHROFF Guardian sensor is connected, it appears in the web interface with type and serial number

Plastic housing

Easy mounting

2 x RJ 45 connection

Easy daisy chain with CAT6 patch cable (or higher shielding)

PRODUKTATTRIBUT

Produkttyp: Givare

Typ: Temperatur, luftfuktighet och digital kontakt

Fungerar med: Guardian Management Gateway

Antal i förpackningen: 1

VARNING

nVent produkter ska installeras och användas endast så som anges i nVents bruksanvisning och utbildningsmaterial. Bruksanvisningar är tillgängliga på www.nvent.com och från din nVent kundtjänstrepresentant. Felaktig installation, missbruk, felapplicering eller annan brist i att helt följa nVents instruktioner och varningar kan orsaka att produkten brister, egendomsskador, allvarliga kroppsskador och dödsfall och/eller ogiltigförklara din garanti.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Vårt starka utbud av varumärken:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE