


EuropacPRO 19" Subrack Kit for DIN Connector, Retrofit Shielding, 3 U, 295 mm

KATALOGNUMMER

24563-193



Non-shielded subrack for Din Connector mounting EN 60603-2 (DIN 41612).

CERTIFIERINGAR



DESIGN

Subrack with side panel type F ("flexible"), front 19" bracket included, depth-adjustable 19" bracket sold separately (not included in items delivered)

Aluminum construction

IP 20, in accordance with IEC 60529

Internal and external dimensions in accordance with: IEC 60297-3-100, -101, IEEE 1101.1

Rear horizontal rails for connector mounting (IEC 60603-2 / DIN 41612)

Modifications such as cutouts, different finishes or dimensions available

Supplied as space-saving flat-pack

Horizontal rail type "light"

PRODUKTATTRIBUT

Rackhöjd: 3U

Djup: 295mm

Antal i förpackningen: 1

För montering: DIN-kontakt

Kortdjup: 160mm; 220mm; 280mm

EMC-packningstyp: Rostfritt stål (kan eftermonteras)

Handtag ingår: Nej

Montage: Rack

Uppfyller: IEC 60297-3-103

EMC-skydd: Nej

Yta: Anodiserad; Passiverad

Material: Aluminium

Produkttyp: Underrack/chassi

Rackbredd: 84HP

Statisk belastning: 11kg

YTTERLIGARE PRODUKTINFORMATION

Individual configuration: broad range of variants in height, width and depth; guide rails for a wide variety of applications; interior options; accessories and mounting material.

VARNING

nVent produkter ska installeras och användas endast så som anges i nVents bruksanvisning och utbildningsmaterial. Bruksanvisningar är tillgängliga på www.nvent.com och från din nVent kundtjänstrepresentant. Felaktig installation, missbruk, felapplicering eller annan brist i att helt följa nVents instruktioner och varningar kan orsaka att produkten brister, egendomsskador, allvarliga kroppsskador och dödsfall och/eller ogiltigförklara din garanti.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab
Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Vårt starka utbud av varumärken:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE