


Intelligent iPDU, EN6450, 400 VAC, 3-PH, 16 A

KATALOGNUMMER

EN6450



Modular, compact intelligent PDU with inlet metering. Ultra-Low Profile Design

DESIGN

Enlogic EN6xxx Intelligent Power Distribution Units monitors input power and power of each individual outlet and offers remote switching of individual outlets, provides billing grade unit level monitoring

High Visibility Data Display and Interactive Graphic Display

Measure circuit breaker loads across redundant feeds to avoid accidental downtime

Enables smart load balancing for power efficiency and maximized capacity utilization

Gigabit Ethernet Interface and redundant Ethernet (10/100)

iPDU DC power redundancy solution for up to 64 PDU's

Toolless Hot-Swap Controller

Input voltage 400 VAC, 3-phase

C13, C19 outlets

PRODUKTATTRIBUT

Produktfamilj: Enlogic

Typ: Intelligent PDU

Produkttyp: Uttagslist

Uttagstyp: (24) C13/C15; (24) C13/C15/C19/C21

Antal uttag: 48

Färg: Svart

Kretsbytare: Ingen kretsbytare

Växlande uttag: Ja

Antal kretsbytare: 0

Effektmärkning: 11,5 kVA i Nordamerika; 11,0 kVA internationellt

Placering av ingångskabel: Toppmatad

Max. ineffekt: 11.5 / 11.0 kVA

Ingångsspänning: 380 – 415V

Fas: 3 PH

Strömbrytare ingår: Ja

Nominell spänning: 415V

Utgångsspänning: 208 – 230VAC

Kontakttyp: IEC 60309 520P6/516P6

Strömstyrka (reducerad strömstyrka): 20 A, (16 A), Nordamerika; 16 A, internationellt

Löstagbar ingångskabel: Nej

Rackenheter: 0U

Material: Stål

Yta: Pulverlackerad

Mätningstyp: Utlopp

Höjd: 1490mm

Bredd: 56mm

Djup: 75mm

Vikt: 12kg

Antal i förpackningen: 1

Längd på ingångskabel: 1.8m

YTTERLIGARE PRODUKTINFORMATION

Please order bracket for vertical mounting separately.

VARNING

nVent produkter ska installeras och användas endast så som anges i nVents bruksanvisning och utbildningsmaterial. Bruksanvisningar är tillgängliga på www.nvent.com och från din nVent kundtjänstrepresentant. Felaktig installation, missbruk, felapplicering eller annan brist i att helt följa nVents instruktioner och varningar kan orsaka att produkten brister,

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Vårt starka utbud av varumärken:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE