


EuropacPRO Advanced EMC Side Panel Cover

Aluminium Side panel 3mm to increase the EMC shielding effect of the subrack by covering the not needed cut-outs.



CERTIFIERINGAR



DESIGN

Side panel covers for increased lateral RF shielding

Assembled on the outside of the standard side panel

Assembly material included

SPECIFIKATIONER

Material:	Aluminium
Produktfamilj:	EuropacPRO
Yta:	Passiverad
Produkttyp:	Sidopanel
Fungerar med:	Underrack
Typ:	Typ H
EMC-skydd:	Ja

Table 1/1

Katalognummer	Rackhöjd	Djup	Antal i förpackningen	Längd	Paketenhet	Snabbleverans
24563-255	3U	175mm	2	175mm	Par	Nej
24563-256	3U	235mm	2	235mm	Par	Nej

Katalognummer	Rackhöjd	Djup	Antal i förpackningen	Längd	Paketenhet	Snabbleverans
24563-257	3U	275mm	2	275mm	Par	Nej
24563-258	3U	277.75mm	2	277.75mm	Par	Nej
24563-259	3U	295mm	2	295mm	Par	Nej
24563-260	3U	355mm	2	355mm	Par	Nej
24563-261	3U	415mm	2	415mm	Par	Nej
24563-262	3U	495mm	2	495mm	Par	Nej
24563-265	4U	175mm	2	175mm	Par	Nej
24563-266	4U	235mm	2	235mm	Par	Nej
24563-267	4U	295mm	2	295mm	Par	Nej
24563-268	4U	355mm	2	355mm	Par	Nej
24563-269	4U	415mm	2	415mm	Par	Nej
24563-270	4U	495mm	2	495mm	Par	Nej
24563-275	6U	175mm	2	175mm	Par	Nej
24563-276	6U	235mm	2	235mm	Par	Nej
24563-277	6U	275mm	2	275mm	Par	Nej
24563-278	6U	277.75mm	2	277.75mm	Par	Nej
24563-279	6U	295mm	2	295mm	Par	Nej
24563-280	6U	355mm	2	355mm	Par	Nej

Katalognummer	Rackhöjd	Djup	Antal i förpackningen	Längd	Paketenhet	Snabbleverans
24563-281	6U	415mm	2	415mm	Par	Nej
24563-282	6U	495mm	2	495mm	Par	Nej

YTTERLIGARE PRODUKTINFORMATION

Side panel and 19" bracket are tox-cold welded together. toxin = Clinching technique, without add aids. This takes place with special tools and high pressure.

9 U version available on request.

VARNING

nVent produkter ska installeras och användas endast så som anges i nVents bruksanvisning och utbildningsmaterial. Bruksanvisningar är tillgängliga på www.nvent.com och från din nVent kundtjänstrepresentant. Felaktig installation, missbruk, felapplicering eller annan brist i att helt följa nVents instruktioner och varningar kan orsaka att produkten brister, egendomsskador, allvarliga kroppsskador och dödsfall och/eller ogiltigförklara din garanti.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Vårt starka utbud av varumärken:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE