

Monitor, Keyboard, Touchpad, 1 U Drawer, Reduced Depth



Designed for standard 19" rackmount designed for comfort
robust design for heavy use or harsh environment operation

CERTIFIERINGAR



DESIGN

Pull-out 17" TFT color monitor chassis, 1 U (resolution Full HD; connects to VGA or DVI-D interface)

Keyboard with different keyboard layout (connects via USB)

Integral touchpad (connects via USB)

Voltage supply: Wide-range input (nominal mains voltage 110 to 240 VAC), Voltage supply 12, 24 and 48 VDC on request

Depth-adjustable mounting for different pitches of server panel/slide mounts; Mounting depth (dimension c = spacing of 19" profiles): dimension c 450 ... 640 mm

With DVI connection

SPECIFIKATIONER

Djup: 400mm
Produkttyp: Skåp/racklåda

Table 1/2

Katalognummer	Rackhöjd	Färg	Färgkod	Typ	Fungerar med	Tangentbordstyp
---------------	----------	------	---------	-----	--------------	-----------------

60118-583	1U	Jet Black	RAL 9005	Bildskärm, tangentbord, pekplatta	19-tumsskåp	QWERTY STORBRITANNI EN
60118-584	1U	Jet Black	RAL 9005	Bildskärm, tangentbord, pekplatta	19-tumsskåp	QWERTZ
60118-585	1U	Jet Black	RAL 9005	Bildskärm, tangentbord, pekplatta	19-tumsskåp	AZERTY (engelskt tangentbordssy stem)

Table 2/2

Katalognummer	Snabbleverans
60118-583	Nej
60118-584	Nej
60118-585	Nej

YTTERLIGARE PRODUKTINFORMATION

Further versions on request – With trackball or numeric pad.

Other Keyboard layouts see user manual.

VARNING

nVent produkter ska installeras och användas endast så som anges i nVents bruksanvisning och utbildningsmaterial. Bruksanvisningar är tillgängliga på www.nvent.com och från din nVent kundtjänstrepresentant. Felaktig installation, missbruk, felapplicering eller annan brist i att helt följa nVents instruktioner och varningar kan orsaka att produkten brister, egendomsskador, allvarliga kroppsskador och dödsfall och/eller ogiltigförklara din garanti.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab
Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Vårt starka utbud av varumärken:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE