


# MultipacPRO 19" Chassis, Aluminum, for Eurocards Assembly



This 19" chassis is a form of subrack which accepts horizontal board mounting or the mounting of non-standard components like transformers or other heavy load accessories typically mounted on a chassis plate. This version are prepared for horizontal PCB board assembly.

## CERTIFIERINGAR



## DESIGN

Aluminum construction

Detachable front and rear panel for easy machining

IP 20, in accordance with IEC 60529

Supplied as space-saving flat-pack

Modifications such as cutouts, different finishes or dimensions available

Internal and external dimensions in accordance with: IEC 60297-3-100, -105

EMC shielding: Approx. 20dB(A) at 2 GHz without shielding material. >40dB(A) at 1 GHz with addition of stainless steel gasket between front panel and case body

Cover and base plate drilled with holes for horizontal mounting of euroboards

## SPECIFIKATIONER

|                       |                         |
|-----------------------|-------------------------|
| <b>Material:</b>      | Aluminium               |
| <b>Yta:</b>           | Anodiserad; Passiverad  |
| <b>Produktfamilj:</b> | MultipacPRO             |
| <b>EMC-skydd:</b>     | Nej (kan eftermonteras) |

**Typ:** Fast  
**Produkttyp:** Underrack/chassi

Table 1/1

| Katalognummer | Rackhöjd | Djup  | Användbar bredd | Montage | Uppfyller                                         | Snabbleverans |
|---------------|----------|-------|-----------------|---------|---------------------------------------------------|---------------|
| 20860-641     | 1U       | 220mm | 403mm           | Rack    | IEC 60297-3-100, IEC 60297-3-101, IEC 60297-3-105 | Nej           |
| 20860-642     | 1U       | 280mm | 403mm           | Rack    | IEC 60297-3-100, IEC 60297-3-101, IEC 60297-3-105 | Nej           |
| 20860-645     | 2U       | 280mm | 403mm           | Rack    | IEC 60297-3-100, IEC 60297-3-101                  | Nej           |

## YTTERLIGARE PRODUKTINFORMATION

Please order front handles separately.

## VARNING

nVent produkter ska installeras och användas endast så som anges i nVents bruksanvisning och utbildningsmaterial. Bruksanvisningar är tillgängliga på [www.nvent.com](http://www.nvent.com) och från din nVent kundtjänstrepresentant. Felaktig installation, missbruk, felapplicering eller annan brist i att helt följa nVents instruktioner och varningar kan orsaka att produkten brister, egendomsskador, allvarliga kroppsskador och dödsfall och/eller ogiltigförklara din garanti.

### North America

All locations  
+1.763.422.2661  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

### Europe

Straubenhardt, Germany  
+49.7082.794.0  
Betschdorf, France  
+33.3.88.90.64.90  
Warsaw, Poland  
+48.22.209.98.35  
Assago, Italy  
+39.02.932.7141  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

### Asia

Shanghai, China  
+86.21.2412.6943  
Qingdao, China  
+86.532.8771.6101  
Singapore  
+65.6768.5800  
Shin-Yokohama, Japan  
+81.45.476.0271  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

### Middle East & India

Dubai, United Arab Emirates  
+971.4.378.1700  
Bangalore, India  
+91.80.6715.2001  
Istanbul, Turkey  
+90.216.250.7374  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)



Vårt starka utbud av varumärken:

**CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE**