

Varistar CP Seismic Base Plate, IP55, One-Piece

The base plate is solid and covers the base of the cabinet.



DESIGN

The base plate is solid and covers the base of the cabinet

Is assembled from outside

SPECIFIKATIONER

Produkttyp: Skåp/rackbas

Kapslingsklass: IP55

Material: Stål

Table 1/2

Katalognummer	Bredd	Djup	Antal i förpackningen	Färg	Färgkod	Uppfyller
20630-301	600mm	600mm	1	Svartgrå	RAL 7021	IEC 61587-1, IEC 61587-2, IEC 60529
20630-302	600mm	800mm	1	Svartgrå	RAL 7021	IEC 61587-1, IEC 61587-2, IEC 60529
20630-303	1000mm	1000mm	1	Svartgrå	RAL 7021	IEC 61587-1, IEC 61587-2, IEC 60529
20630-304	600mm	1200mm	1	Svartgrå	RAL 7021	IEC 61587-1, IEC 61587-2, IEC 60529

Katalognummer	Bredd	Djup	Antal i förpackningen	Färg	Färgkod	Uppfyller
20630-305	800mm	600mm	1	Svartgrå	RAL 7021	IEC 61587-1, IEC 61587-2, IEC 60529
20630-306	800mm	800mm	1	Svartgrå	RAL 7021	IEC 61587-1, IEC 61587-2, IEC 60529
20630-307	800mm	1000mm	1	Svartgrå	RAL 7021	IEC 61587-1, IEC 61587-2, IEC 60529
20630-308	1200mm	1200mm	1	Svartgrå	RAL 7021	IEC 61587-1, IEC 61587-2, IEC 60529

Table 2/2

Katalognummer	Yta	Typ	Fungerar med	Snabbleverans
20630-301	Pulverlackerad	Basplatta, standard	Varistar CP	Nej
20630-302	Pulverlackerad	Basplatta, standard	Varistar CP	Nej
20630-303	Pulverlackerad	Basplatta, standard	Varistar CP	Nej
20630-304	Pulverlackerad	Basplatta, standard	Varistar CP	Nej
20630-305	Pulverlackerad	Basplatta, standard	Varistar CP	Nej
20630-306	Pulverlackerad	Basplatta, standard	Varistar CP	Nej
20630-307	Pulverlackerad	Basplatta, standard	Varistar CP	Nej
20630-308	Pulverlackerad	Basplatta, standard	Varistar CP	Nej

YTTERLIGARE PRODUKTINFORMATION

This base plate is used for applications which don't require cable entry from the base.

Please purchase the grounding kit separately.

VARNING

nVent produkter ska installeras och användas endast så som anges i nVents bruksanvisning och utbildningsmaterial. Bruksanvisningar är tillgängliga på www.nvent.com och från din nVent kundtjänstrepresentant. Felaktig installation, missbruk, felapplicering eller annan brist i att helt följa nVents instruktioner och varningar kan orsaka att produkten brister, egendomsskador, allvarliga kroppsskador och dödsfall och/eller ogiltigförklara din garanti.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Vårt starka utbud av varumärken:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE