

# MS PDU, 0U, 100A(80A)NA/100A Int, 380-415V, 3P Wye, 24 CB, 48 Locking Combo

## Data Solutions

### 物料号

**EN2990**

The Advantage Series Input Metered, Outlet Switched PDU family offers energy metering with advanced power and environmental monitoring options and remote outlet on/off switching. Comprehensive monitoring at both the input phase and circuit breaker levels offers advanced alerts of potential overloads. Billing-grade metering provides accurate power consumption data for energy use optimization. The hot-swappable network management controller features Gigabit and redundant ethernet communication with advanced support for external environmental sensors and rack security access solutions.

### 功能

IEC 62368 listed. RoHS, and REACH compliant. See drawing for additional information

UL 2900-1 certified for safety software cybersecurity for network-connectable products

Dual network connectivity ports: 1x Gigabit Ethernet (10/100/1000 Mbps) and 1x (10/100 Mbps) connection/IP address

Ethernet cascading up to 64 PDUs. Each PDU can provide DC power sufficient to power network management electronics

Dual Ethernet ports for redundant network communications

Remote connectivity through HTTP(s), IPv4 and IPv6, SSH, Virtual Serial, SNMP (v1, v2c, v3), JSON-RPC, LDAP(S)

Data efficient REACT framework with native mobile device support

Tool-less hot swappable Network Management Card (NMC) with Cortex A-5 for microprocessing and memory that can be installed both upright and upside down for top or bottom power inputs

The border color of the NMC display is user programmable for power source identification by PDU

The NMC supports up to 10 digital sensors for environmental and/or electronic lock monitoring

Display languages include English, Spanish, German, French, Italian, Korean, Japanese, and Chinese (simplified)

## 产品属性

产品系列: Enlogic

类型: 智能 PDU

产品类型: 插排

插座类型: (24) 锁定 C13/C15; (24) 锁定 C13/C15/C19/C21

插座数量: 48

颜色: 黑色

开关插座: 是

电缆长度: 1800mm

断路器: 20 A, 1 极, Hy-MagA

额定功率: 57.6 kVA 北美; 69 kVA 国际

断路器数量: 24

标称输出功率: 230VAC

标称电压: 415V

包含通/断开关: 是

电流 (降额电流) : 100 A (80 A) 北美; 100 A 国际

输出电压: 208 – 230VAC

机架单元: 0U

插头类型: IEC 60309 5125P6W (IP67)

计量类型: 输入

可拆卸输入电缆: 否

材料: 钢

完成: 粉末涂层

高度: 2030mm

宽度: 85mm

深度: 85mm

包装数量: 1

输入电缆长度: 1.8m

## 其他产品详情

---

Warranty : nVent Enlogic branded equipment provided shall be free from manufacturing defects for a period of five (5) years from the invoice date to the original purchaser.

## 警告

---

应仅根据 nVent 的产品说明书与培训材料安装并使用 nVent 的产品。可访问 [www.nvent.com](http://www.nvent.com) 获取说明书，或者向您的 nVent 客服代表索取。错误安装、使用不当、滥用或未能完全遵守 nVent 的说明与警告，可能会造成产品故障、财产损失、严重的人身伤害及死亡和/或使得保修服务无效。



我们强大的品牌组合:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE