

WLock 线 C13/C14, 1.8 米, 蓝色, 100 个

Data Solutions

物料号

EP1314B72X100



Secure dual W-Lock power cords provide enhanced cord retention between both the PDU and IT equipment. Both connections require deliberate action in order to release the locking buttons to prevent accidental detachment of power connections. Cords function with any corresponding standard IEC receptacle, but locking feature requires compatible W-lock or V-lock outlets

功能

安全的双锁电源线

IEC C14/C20 插头将锁定到任何 RackPower PDU 中

通用锁定 IEC 连接器将安全地锁定到任何标准 C14/C20 电源插座中

对于两种连接方式，都需要特定操作才能松开锁定按钮并断开电源

产品属性

产品类型: 电缆

产品系列: Enlogic

类型: 电缆

搭配: RackPower

长度: 1800mm

颜色: 蓝色

高度: 270mm

输入电缆长度: 1.764m

包装数量: 100

插头类型: C13/C14

可拆卸输入电缆: 否

警告

应仅根据 nVent 的产品说明书与培训材料安装并使用 nVent 的产品。可访问 www.nvent.com 获取说明书，或者向您的 nVent 客服代表索取。错误安装、使用不当、滥用或未能完全遵守 nVent 的说明与警告，可能会造成产品故障、财产损失、严重的人身伤害及死亡和/或使得保修服务无效。



我们强大的品牌组合:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE

©2025 nVent。所有 nVent 标志和徽标均由 nVent Services GmbH 或其附属公司拥有或授权。所有其他商标均为其各自所有者的财产。nVent 保留更改规格的权利，恕不另行通知。

本文档由系统生成。