

RackChiller RDHX PRO Passive, Right Hinged

Data Solutions

背门冷却器还可以进行改造，以适用于大多数第三方机架。

市场上体积小巧的背门冷却器，同时具有非常高的每千瓦冷却能力。

The new rear door cooling units from nVent are offered in a range of standard sizes for use with 42U, 47U, in both 600mm and 800mm widths (other sizes available on request). The coolers themselves are 250mm deep, with a dry weight of 140Kg. One of the features of rear door coolers is they are compact and do not require any additional floor space or ceiling headroom – in fact, their use can free up white space as CRAH units and other room cooling equipment may be eliminated from the data centre.

RDHX PRO Passive is fanless device than can be upgraded to Active with the addition of the fan modules. Meaning you can scale your data center to the requirements of your server racks. With no fans, the power consumption is near zero. This also reduces the service and maintenance costs with minimal components.



功能

背门冷却器冷却水

热插拔组件可简化维修，并最大限度地提高可用性

设计为可在设备水温升高的情况下高效运行

与芯片液体冷却相结合

模块化标准 - 可轻松满足各种要求

即使在安装和调试后也可升级为主动式设备

电源, 控制器和控制阀均支持热插拔

自动阀开启控制

7” 高分辨率触摸屏界面

通过顶部或底部进行液压和电气连接

通过以太网接口监测（网页浏览器, Modbus TCP, SNMP v2c) 和 Modbus RTU

技术参数

Table 1/3

物料号	产品类型	产品系列	机架高度	颜色代码	防护等级	宽度
10630-215	空气/液体热交换器	RackChiller	47U	RAL 7021	IP20	800mm
10630-213	空气/液体热交换器	RackChiller	42U	RAL 7021	IP20	800mm
10630-214	空气/液体热交换器	RackChiller	47U	RAL 7021	IP20	600mm
10630-212	空气/液体热交换器	RackChiller	42U	RAL 7021	IP20	600mm

Table 2/3

物料号	深度	高度	电源电压	冷却剂进给装置	完成	材料
10630-215	280mm	2200mm	195 – 277V	底部, 顶部	粉末涂层	钢
10630-213	280mm	2000mm	195 – 277V	底部, 顶部	粉末涂层	钢
10630-214	280mm	2200mm	195 – 277V	底部, 顶部	粉末涂层	钢
10630-212	280mm	2000mm	195 – 277V	底部, 顶部	粉末涂层	钢

Table 3/3

物料号	包装数量
10630-215	1
10630-213	1

物料号	包装数量
10630-214	1
10630-212	1

其他产品详情

对于气/液热交换器的无故障操作，必须保持冷却剂的质量要求；选择合适的防腐蚀和霜冻保护剂取决于使用设备的环境和外部冷却器。

冷却剂温度低于 14 °C 时，冷凝风险增加。建议使用冷凝水管理包。

警告

应仅根据 nVent 的产品说明书与培训材料安装并使用 nVent 的产品。可访问 www.nvent.com 获取说明书，或者向您的 nVent 客服代表索取。错误安装、使用不当、滥用或未能完全遵守 nVent 的说明与警告，可能会造成产品故障、财产损失、严重的人身伤害及死亡和/或使得保修服务无效。



我们强大的品牌组合:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE