

Telescopic Slides C-Profile for Cabinet

Data Solutions



Telescopic slides with guiding profile for fitting in cabinets with 25 kg load capacity.

认证



功能

For mounting 84 HP wide subracks in the 19" plane

Loading capacity: 25 kg per pair

The guiding profile (1) is matched to the fixing dimension in the cabinet (it is bolted to the 19" profile of the cabinet); the adaptor Rail (3) is matched to the depth and fixing dimension on the subrack (it is inserted into the guiding profile like a telescopic slide)

技术参数

材料:	铝
完成:	阳极氧化
类型:	C 形型材
产品类型:	伸缩滑轨

Table 1/1		
物料号	深度	包装数量
24562-460	500mm	2
24562-464	600mm	2
24562-461	600mm	2
24562-466	800mm	2
24562-474	800mm	2
24562-467	900mm	2
24562-468	1000mm	2
24562-472	1100mm	2
24562-473	1200mm	2

其他产品详情

No protection against extraction, no stop at full extension.

The reinforcement Rail and the C-Rails have been tested in accordance with the Russian atomic energy authority GAN standards.

警告

应仅根据 nVent 的产品说明书与培训材料安装并使用 nVent 的产品。可访问 www.nvent.com 获取说明书，或者向您的 nVent 客服代表索取。错误安装、使用不当、滥用或未能完全遵守 nVent 的说明与警告，可能会造成产品故障、财产损失、严重的人身伤害及死亡和/或使得保修服务无效。



我们强大的品牌组合:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE