

# Mounting profiles, CLPF, 40x725x25mm, Zinc Plated, Mild Steel

## 物料号

### CLPF800



The mounting profiles can be fixed in all directions, providing full flexibility for the mounting of accessories, components, and other equipment.

## 功能

Description: The CLPF profile system is a 40 mm wide and 25 mm high profile, which can be mounted in all directions on the enclosure's frame. It can also be used in combination with the CLPK and the VB profiles. By turning the profile it can be used as a standard CP20/40 profile in combination with GLM 40/6 sliding nut, to mount installation material which needs adjusting in depth. The profiles, when mounted onto the enclosure's frame are flush with the enclosure's profiles. Two rows of hole patterns for cage nut fixing and self tapping screws are provided. For 90 mm wide profiles two profiles can be mounted next to each other.

Material: Zinc plated steel.

Pack quantity: 4 profiles including snap-line for fixing.

## 产品属性

订货号: CLPF800

高度: 40mm

宽度: 725mm

深度: 25mm

兼容的外壳高度: 800mm min

兼容的外壳宽度: 800mm min

兼容的外壳深度: 800mm min

最大水平负载 C: 800 N

最大水平负载: 1000 N

材料: 低碳钢

完成: 镀锌

厚度: 1.5mm

包装数量: 4

重量: 2.8kg

外壳材料: 低碳钢

## 警告

应仅根据 nVent 的产品说明书与培训材料安装并使用 nVent 的产品。可访问 [www.nvent.com](http://www.nvent.com) 获取说明书，或者向您的 nVent 客服代表索取。错误安装、使用不当、滥用或未能完全遵守 nVent 的说明与警告，可能会造成产品故障、财产损失、严重的人身伤害及死亡和/或使得保修服务无效。



我们强大的品牌组合:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE