

Ventilation Roofs, CVR, 58x800x400mm, Zinc Plated, Mild Steel

物料号

CVR0804R5

通风顶盖提供了经济有效的自然通风，同时防止昆虫和灰尘进入。



功能

Description: Raised roof with 2.5 mm ventilation slots and filter material.

Material: 1.5 mm steel plate. Filter material: EU 4 according to DIN 24185.

Finish: RAL 7035 structured powder coating.

Temperature resistance: 100 °C.

Protection: Complies with IP 31, TYPE 1.

Pack quantity: 1 piece with mounting brackets and ventilation filter.

Note: Increases the enclosure height by 40 mm.

产品属性

订货号: CVR0804R5

高度: 58mm

宽度: 800mm

深度: 400mm

产品系列: 独立

材料: 低碳钢

完成: 粉末涂层

颜色: 浅灰色

颜色代码: RAL 7035

厚度: 1.5mm

包装数量: 1

重量: 4.8kg

外壳材料: 低碳钢

警告

应仅根据 nVent 的产品说明书与培训材料安装并使用 nVent 的产品。可访问 www.nvent.com 获取说明书，或者向您的 nVent 客服代表索取。错误安装、使用不当、滥用或未能完全遵守 nVent 的说明与警告，可能会造成产品故障、财产损失、严重的人身伤害及死亡和/或使得保修服务无效。



我们强大的品牌组合:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE