

Inner Doors For Power Distribution, DI, 1753x765x53mm, Light Gray, Mild Steel

物料号

DI1808R5



内门为标准或玻璃前门后面的设备提供可转动的安装表面，可覆盖其他元器件，并防止未经授权的操作。

功能

Description: Inner door provides a hinged mounting surface for equipment behind a standard or glazed front door. A mounting space of 80 mm, is available between the doors when the inner door is in the most forward position. Can be adjusted in depth by steps of 25 mm. The mounting plate remains usable behind the inner door. The door is equipped with two double-bit 3 mm locks.

Material: 1.5 mm mild steel.

Finish: RAL 7035 structured powder coating.

Pack quantity: 1 door with mounting accessories.

产品属性

订货号: DI1808R5

高度: 1753mm

宽度: 765mm

深度: 53mm

外壳材料: 低碳钢

产品系列: 独立

材料: 低碳钢

完成: 粉末涂层

颜色: 浅灰色

颜色代码: RAL 7035

厚度: 1.5mm

包装数量: 1

重量: 26.4kg

其他产品详情

Other sizes available on request.

警告

应仅根据 nVent 的产品说明书与培训材料安装并使用 nVent 的产品。可访问 www.nvent.com 获取说明书，或者向您的 nVent 客服代表索取。错误安装、使用不当、滥用或未能完全遵守 nVent 的说明与警告，可能会造成产品故障、财产损失、严重的人身伤害及死亡和/或使得保修服务无效。



我们强大的品牌组合:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE