

层板 19 英寸，VSF



This shelf can be adjusted in height and provides further mounting possibilities with a higher loading capacity. It also has ventilation openings to ensure for proper air circulation within the enclosure.

功能

Description: Maximum loading capacity when mounted directly onto the 19" profiles, front and rear. Ventilation openings.

Material: 1.5 mm steel.

Finish: RAL 7035.

Pack quantity: 1 shelf with mounting material.

Maximum load capacity: 1200 N

技术参数

厚度: 1.5mm

颜色: 浅灰色

材料: 低碳钢

完成: 粉末涂层

颜色代码: RAL 7035

Table 1/1						
物料号	订货号	高度	宽度	深度	额定负载	外壳材料
VSF1406	VSF1406	19mm	404mm	404mm	1200N	低碳钢
VSF1470	VSF1470	19mm	468mm	468mm	1200N	低碳钢
VSF1597	VSF1597	19mm	595mm	595mm	1200N	低碳钢

警告

应仅根据 nVent 的产品说明书与培训材料安装并使用 nVent 的产品。可访问 www.nvent.com 获取说明书，或者向您的 nVent 客服代表索取。错误安装、使用不当、滥用或未能完全遵守 nVent 的说明与警告，可能会造成产品故障、财产损失、严重的人身伤害及死亡和/或使得保修服务无效。



我们强大的品牌组合:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE