

伸缩通风层板（框架）



This shelf can be extracted to allow for the inspection and maintenance of installed components. It has ventilation openings to ensure for proper air circulation within the enclosure.

功能

Description: For easy access to installed equipment. Mounted directly to the enclosure's frame. Partial depth mounting is an option. Possibility to take the shelf out of the slides even after mounting into the enclosure. Reversed and side mounting possible.

Material: 2 mm zinc plated steel.

Maximum load: 500 N.

Pack quantity: 1 ventilated shelf and 1 pair of telescopic slides with mounting accessories.

Mounting requirements: Add SHTP profiles for full/partial depth installation to the enclosure's frame.

技术参数

厚度: 2mm

材料: 低碳钢

完成: 镀锌

| Table 1/1 | | | | | | |
|-----------|---------|------|-------|-------|-------|--------|
| 物料号 | 订货号 | 高度 | 宽度 | 深度 | 安装板宽度 | 最大安装深度 |
| SHT0606 | SHT0606 | 46mm | 600mm | 600mm | 460mm | 550mm |
| SHT0608 | SHT0608 | 46mm | 600mm | 800mm | 460mm | 750mm |
| SHT0806 | SHT0806 | 46mm | 800mm | 600mm | 660mm | 550mm |
| SHT0808 | SHT0808 | 46mm | 800mm | 800mm | 660mm | 750mm |

警告

应仅根据 nVent 的产品说明书与培训材料安装并使用 nVent 的产品。可访问 www.nvent.com 获取说明书，或者向您的 nVent 客服代表索取。错误安装、使用不当、滥用或未能完全遵守 nVent 的说明与警告，可能会造成产品故障、财产损失、严重的人身伤害及死亡和/或使得保修服务无效。



我们强大的品牌组合:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE