

V 系列中型空调



V-Series Mid-Size Air Conditioners are designed to deliver vital cooling to sensitive electronics. They meet a broad range of cooling requirements, including an all metal shroud to stand up to rugged factory conditions. Units have operating temperature ranges from 20°C to 55°C for indoor models and -40°C to 55°C for outdoor models. The coils are coated for filterless operation in most manufacturing environments or an optional aluminum filter can be used. Each unit is rigorously tested to withstand shipping vibration, high temperatures and other operating challenges.

工业标准

IP34 环境侧，IP56 机柜侧

功能

库存型号在机柜侧配备机械温控器

易于安装和更换网状过滤器

紧凑型设计可最大限度地减少机柜占地，并在相同整体尺寸下最大限度地提高冷却能力

外表面安装标准

Stock models approved by CE, NEMA 4, IP56 protection class

When properly installed to enclosure at the same protection level, it can achieve NEMA 4, IP56 rain-protection level

Operating temperature range from -40 C to 55 C

100% functionally tested

Refrigerant: R134a

Power input: terminal block

Controller: mechanical temperature controller

Thermostat location: enclosure side

Factory thermostat setting (F/C): 86/30

技术参数

颜色： 浅灰色

材料： 低碳钢

完成： 粉末涂层

颜色代码： RAL 7035

Table 1/1						
物料号	高度	宽度	深度	标称电压	远程访问控制	相数
VA081225G050S	724mm	432mm	236mm	220V	否	1Ph
VA081225G060S	724mm	432mm	236mm	220V	否	1Ph
VA081225G070S	724mm	432mm	236mm	220V	否	1Ph
VA081225G150S	724mm	432mm	236mm	220V	否	1Ph
VA081225G160S	724mm	432mm	236mm	220V	否	1Ph
VA081525G050S	724mm	432mm	236mm	220V	否	1Ph
VA081525G060S	724mm	432mm	236mm	220V	否	1Ph
VA081525G070S	724mm	432mm	236mm	220V	否	1Ph
VA081525G150S	724mm	432mm	236mm	220V	否	1Ph
VA081525G160S	724mm	432mm	236mm	220V	否	1Ph
VA082025G050S	724mm	432mm	236mm	220V	否	1Ph
VA082025G060S	724mm	432mm	236mm	220V	否	1Ph
VA082025G070S	724mm	432mm	236mm	220V	否	1Ph
VA082025G150S	724mm	432mm	236mm	220V	否	1Ph
VA082025G160S	724mm	432mm	236mm	220V	否	1Ph

物料号	高度	宽度	深度	标称电压	远程访问控制	相数
VA081545G410H	724mm	432mm	236mm	380V	否	3Ph
VA081545G410S	724mm	432mm	236mm	380V	否	3Ph
VA082045G410H	724mm	432mm	236mm	380V	否	3Ph
VA082045G410S	724mm	432mm	236mm	380V	否	3Ph

警告

应仅根据 nVent 的产品说明书与培训材料安装并使用 nVent 的产品。可访问 www.nvent.com 获取说明书，或者向您的 nVent 客服代表索取。错误安装、使用不当、滥用或未能完全遵守 nVent 的说明与警告，可能会造成产品故障、财产损失、严重的人身伤害及死亡和/或使得保修服务无效。



我们强大的品牌组合:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE