

通风顶盖，CVR

通风顶盖提供了经济有效的自然通风，同时防止昆虫和灰尘进入。



功能

Description: Raised roof with 2.5 mm ventilation slots and filter material.

Material: 1.5 mm steel plate. Filter material: EU 4 according to DIN 24185.

Finish: RAL 7035 structured powder coating.

Temperature resistance: 100 °C.

Protection: Complies with IP 31, TYPE 1.

Pack quantity: 1 piece with mounting brackets and ventilation filter.

Note: Increases the enclosure height by 40 mm.

技术参数

厚度: 1.5mm
颜色: 浅灰色
材料: 低碳钢
完成: 粉末涂层
颜色代码: RAL 7035

Table 1/1						
物料号	订货号	高度	宽度	深度	产品系列	外壳材料
CVR0505R5	CVR0505R5	58mm	500mm	500mm	独立	低碳钢
CVR0603R5	CVR0603R5	58mm	600mm	300mm	独立	低碳钢
CVR0604R5	CVR0604R5	58mm	600mm	400mm	独立	低碳钢
CVR0605R5	CVR0605R5	58mm	600mm	500mm	独立	低碳钢
CVR0606R5	CVR0606R5	58mm	600mm	600mm	独立	低碳钢
CVR0608R5	CVR0608R5	58mm	600mm	800mm	独立	低碳钢
CVR0803R5	CVR0803R5	58mm	800mm	300mm	独立	低碳钢
CVR0804R5	CVR0804R5	58mm	800mm	400mm	独立	低碳钢
CVR0805R5	CVR0805R5	58mm	800mm	500mm	独立	低碳钢
CVR0806R5	CVR0806R5	58mm	800mm	600mm	独立	低碳钢
CVR0808R5	CVR0808R5	58mm	800mm	800mm	独立	低碳钢
CVR0809R5	CVR0809R5	58mm	800mm	900mm	独立	低碳钢
CVR1003R5	CVR1003R5	58mm	1000mm	300mm	独立	低碳钢
CVR1004R5	CVR1004R5	58mm	1000mm	400mm	独立	低碳钢

物料号	订货号	高度	宽度	深度	产品系列	外壳材料
CVR1005R5	CVR1005R5	58mm	1000mm	500mm	独立	低碳钢
CVR1006R5	CVR1006R5	58mm	1000mm	600mm	独立	低碳钢
CVR1008R5	CVR1008R5	58mm	1000mm	800mm	独立	低碳钢
CVR1203R5	CVR1203R5	58mm	1200mm	300mm	独立	低碳钢
CVR1204R5	CVR1204R5	58mm	1200mm	400mm	独立	低碳钢
CVR1205R5	CVR1205R5	58mm	1200mm	500mm	独立	低碳钢
CVR1206R5	CVR1206R5	58mm	1200mm	600mm	独立	低碳钢
CVR1208R5	CVR1208R5	58mm	1200mm	800mm	独立	低碳钢
CVR1604R5	CVR1604R5	58mm	1600mm	400mm	独立	低碳钢
CVR1605R5	CVR1605R5	58mm	1600mm	500mm	独立	低碳钢
CVR1606R5	CVR1606R5	58mm	1600mm	600mm	独立	低碳钢

警告

应仅根据 nVent 的产品说明书与培训材料安装并使用 nVent 的产品。可访问 www.nvent.com 获取说明书，或者向您的 nVent 客服代表索取。错误安装、使用不当、滥用或未能完全遵守 nVent 的说明与警告，可能会造成产品故障、财产损失、严重的人身伤害及死亡和/或使得保修服务无效。



我们强大的品牌组合:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE