

nVent LENTON Quick Wedge Replacement Pin



Wedge pins are provided with the purchase of couplers. Replacement wedge pins are made available as a convenience, should any get lost on the jobsite.

功能

Package comes with twenty-six replacement wedge pins and one grommet

Designed to withstand the forces required for assembly

技术参数

材料: 钢

Table 1/2

物料号	订货号	完成	钢筋尺寸, 公制	钢筋尺寸, 美国	钢筋尺寸, 加拿大	直径 (Ø)
ML4PKG26	145860	普通	12 mm	#4	10M	13 mm
ML4GPKG26		机械镀锌	12 mm	#4	10M	13 mm
ML5PKG26	145870	普通	16 mm	#5	15M	13 mm
ML5GPKG26		机械镀锌	16 mm	#5	15M	13 mm


物料号	订货号	完成	钢筋尺寸，公制	钢筋尺寸，美国	钢筋尺寸，加拿大	直径 (Ø)
ML6PKG26	145880	普通	20 mm	#6	20M	16 mm
ML6GPKG26		机械镀锌	20 mm	#6	20M	16 mm

Table 2/2			
物料号	订货号	长度 (L)	单位重量
ML4PKG26	145860	40mm	0.03 kg
ML4GPKG26		40mm	0.03 kg
ML5PKG26	145870	46mm	0.04 kg
ML5GPKG26		46mm	0.04 kg
ML6PKG26	145880	53mm	0.06 kg
ML6GPKG26		53mm	0.06 kg

其他产品详情

Prior to installation, please read and understand the detailed instructions and safety notices provided in the nVent LENTON Quick Wedge Operator's Manual.

图



警告

应仅根据 nVent 的产品说明书与培训材料安装并使用 nVent 的产品。可访问 www.nvent.com 获取说明书，或者向您的 nVent 客服代表索取。错误安装、使用不当、滥用或未能完全遵守 nVent 的说明与警告，可能会造成产品故障、财产损失、严重的人身伤害及死亡和/或使得保修服务无效。

北美

+1.800.753.9221
，按 1 转客户服务
，按 2 转技术支持

欧洲

荷兰：
+31 800-0200135
法国：
+33 800 901 793

欧洲

德国：
800 1890272
其他国家/地区：
+31 13 5835404

亚太地区

上海：
+ 86 21 2412 1618/19
悉尼：
+61 2 9751 8500



我们强大的品牌组合：

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE