

Varistar CP Steel Door, Perforated With 1-Point Locking, Key Plate Only, RAL 7021, 29 U, 1400H 800W

Power Utilities

物料号

21630-510



Varistar CP Perforated Steel Door Single Point Locking for IP 20 applications.

功能

Perforated steel door with single point locking for IP 20 protection class

Lever handle with built-in push button

Opening angle 180°

Key lock cover

产品属性

产品类型: 机柜门

产品系列: Varistar CP

类型: 钢制门, 网孔

搭配: Varistar CP

锁定类型: 单点锁定

颜色: 暗灰色

颜色代码: RAL 7021

机架高度: 29 U

高度: 1400 mm

宽度: 800 mm

防护等级: IP20

符合: IEC 61587-1

其他产品详情

Please order lever handle and DIN profile half cylinder separately.

Please purchase the grounding kit separately.

警告

应仅根据 nVent 的产品说明书与培训材料安装并使用 nVent 的产品。可访问 www.nvent.com 获取说明书，或者向您的 nVent 客服代表索取。错误安装、使用不当、滥用或未能完全遵守 nVent

的说明与警告，可能会造成产品故障、财产损失、严重的人身伤害及死亡和/或使得保修服务无效。



我们强大的品牌组合:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE