

Varistar CP Glazed Door With 3-Point Locking, RAL 7021, 38 U, 1800H 600W, IP55

Power Utilities

物料号

21630-723



Glass door with 3 point locking allows stronger adhesion between door and the cabinet frame. This prevents the metal measurability to show and provides the door extra robustness.

功能

Glazed Door With 3-Point Locking, With Lock

Lever handle with key insert (2 keys)

Opening angle 180°

Security glass, 6 mm

Standard fitting, lock on right-hand door

Can be retrofitted with lever handle 24630003 and DIN profile half cylinder with keys or push button

产品属性

产品类型: 机柜门

产品系列: Varistar CP

类型: 玻璃门

搭配: Varistar CP

锁定类型: 3 点锁定

材料: 钢; 玻璃

完成: 粉末涂层

颜色: 暗灰色

颜色代码: RAL 7021

机架高度: 38 U

高度: 1800 mm

宽度: 600 mm

防护等级: IP55

符合: IEC 61587-1

其他产品详情

Please order DIN profile half cylinder for lever handle 24630003 separately.

Please purchase the grounding kit separately.

警告

应仅根据 nVent 的产品说明书与培训材料安装并使用 nVent 的产品。可访问 www.nvent.com 获取说明书，或者向您的 nVent 客服代表索取。错误安装、使用不当、滥用或未能完全遵守 nVent 的说明与警告，可能会造成产品故障、财产损失、严重的人身伤害及死亡和/或使得保修服务无效。



我们强大的品牌组合:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE