

Straight Section Lay-in Hinged-Cover Type 1 no KOs, 6x6x120, Gray, Steel

电力公用事业

物料号

F66G120



Lay-in Hinged-Cover Type 1 Straight Sections are used for enclosing wire and cable in wireway runs. Sections are completely open on one side so wires and cables can be laid in along wireway run.

无需穿过电线或线缆，可以防止损坏绝缘层，穿过式布线系统经常出现这种情况。Sections are available in lengths from 12 inch to 120 inch, with or without knockouts.

功能

Lay-in Hinged-Cover Type 1 Straight Sections are used for enclosing wire and cable in wireway runs

Sections are completely open on one side so wires and cables can be laid in along wireway run

No pulling through of wires or cables prevents damage to insulation that often occurs in a pull-through wiring system

Sections are available in lengths from 12 inch to 120 inch, with or without knockouts

注意：F1212GXX catalog numbers without "H" are not hinged. F1212GXXH catalog numbers are hinged

产品属性

Article Number: 52390

类型：直线桥架

高度：152 mm

宽度：152 mm

深度：3048 mm

保护等级：NEMA Type 1; IP30

材料：低碳钢

表面：粉末涂层

颜色：灰色

颜色代码：ANSI 61

厚度：1.52 mm

ADDITIONAL PRODUCT DETAILS

F1212GXX catalog numbers without "H" are not hinged. F1212GXXH catalog numbers are hinged.

警告

应仅根据 nVent 的产品说明书与培训材料安装并使用 nVent 的产品。可访问 www.nvent.com 获取说明书，或者向您的 nVent 客服代表索取。错误安装、使用不当、滥用或未能完全遵守 nVent 的说明与警告，可能会造成产品故障、财产损失、严重的人身伤害及死亡和/或使得保修服务无效。



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE