

EuropacPRO 19" Subrack Kit for Backplane, Heavy, Retrofit Shielding, Front Handle

电力公用事业

用于安装背板的非 EMC 屏蔽型插箱，重型版本带有 tox 连接侧板和前把手。



认证



功能

Subrack with side panel type H ("Heavy"), 19" bracket is firmly fixed to side panel (tox-cold welded)

扁平包装，节省空间

用于安装背板的后水平横梁，带绝缘条

“重”型水平横梁

Shock and Vibration resistance up to 5 g

IP 20, in accordance with IEC 60529

Shock and vibration tested to the German "Bahn" standards BN 411002, BN 411003

内部和外部尺寸符合：IEC 60297-3-100, -101, IEEE 1101.1

Installed load up to 15 kg

此版本带前把手

技术参数

Table 1/3						
物料号	机架高度	深度	包装数量	用于安装	板深度	EMC 垫片类型
24567-161	3 U	175 mm	1	背板	160 mm	不锈钢
24567-162	3 U	235 mm	1	背板	160 mm, 220 mm	不锈钢
24567-163	3 U	295 mm	1	背板	160 mm, 220 mm, 280 mm	不锈钢
24567-164	3 U	355 mm	1	背板	160 mm, 220 mm, 280 mm, 340 mm	不锈钢
24567-461	6 U	175 mm	1	背板	160 mm	不锈钢
24567-462	6 U	235 mm	1	背板	160 mm, 220 mm	不锈钢
24567-463	6 U	295 mm	1	背板	160 mm, 220 mm, 280 mm	不锈钢
24567-464	6 U	355 mm	1	背板	160 mm, 220 mm, 280 mm, 340 mm	不锈钢

Table 2/3						
物料号	耐冲击和振动性	包含把手	安装	符合	EMC 屏蔽	产品类型
24567-161	5 g (force)	是	机架	IEC 60297-3-103	否	插箱/机箱
24567-162	5 g (force)	是	机架	IEC 60297-3-103	否	插箱/机箱
24567-163	5 g (force)	是	机架	IEC 60297-3-103	否	插箱/机箱
24567-164	5 g (force)	是	机架	IEC 60297-3-103	否	插箱/机箱
24567-461	5 g (force)	是	机架	IEC 60297-3-103	否	插箱/机箱

物料号	耐冲击和振动性	包含把手	安装	符合	EMC 屏蔽	产品类型
24567-462	5 g (force)	是	机架	IEC 60297-3-103	否	插箱/机箱
24567-463	5 g (force)	是	机架	IEC 60297-3-103	否	插箱/机箱
24567-464	5 g (force)	是	机架	IEC 60297-3-103	否	插箱/机箱

Table 3/3			
物料号	机架宽度	静态负载	认证
24567-161	84 HP	15 kgf	RoHS
24567-162	84 HP	15 kgf	RoHS, DB
24567-163	84 HP	15 kgf	RoHS, DB
24567-164	84 HP	15 kgf	RoHS, DB
24567-461	84 HP	15 kgf	RoHS, DB
24567-462	84 HP	15 kgf	RoHS, DB
24567-463	84 HP	15 kgf	RoHS, DB
24567-464	84 HP	15 kgf	RoHS, DB

ADDITIONAL PRODUCT DETAILS

单个配置：支持大范围高度、宽度和深度；根据不同应用可选多种规格导轨；内部选项；附件和安装材料。

警告

应仅根据 nVent 的产品说明书与培训材料安装并使用 nVent 的产品。可访问 www.nvent.com 获取说明书，或者向您的 nVent 客服代表索取。错误安装、使用不当、滥用或未能完全遵守 nVent 的说明与警告，可能会造成产品故障、财产损失、严重的人身伤害及死亡和/或使得保修服务无效。



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE