

EuropacPRO 19" Subrack Kit for Backplane, Light, Unshielded

Power Utilities

Non-EMC shielded subrack for backplane mounting, light version.



认证



功能

Subrack with side panel type L ("light") with integrated 19" support brackets

Horizontal rail type "light"

Aluminum construction

Rear horizontal rails for backplane mounting with insulation strip

Installed load up to 7.5 kg

Supplied as space-saving flat-pack

Internal and external dimensions in accordance with: IEC 60297-3-100, -101, IEEE 1101.1

Modifications such as cutouts, different finishes or dimensions available

技术参数

Table 1/2						
物料号	机架高度	深度	包装数量	用于安装	板深度	包含手柄
24564-433	6 U	295 mm	1	背板	160 mm, 220 mm, 280 mm	否
24564-432	6 U	235 mm	1	背板	160 mm, 220 mm	否
24564-431	6 U	175 mm	1	背板	160 mm	否
24564-133	3 U	295 mm	1	背板	160 mm, 220 mm, 280 mm	否
24564-132	3 U	235 mm	1	背板	160 mm, 220 mm	否
24564-131	3 U	175 mm	1	背板	160 mm	否

Table 2/2						
物料号	安装	符合	EMC 屏蔽	产品类型	机架宽度	静态负载
24564-433	机架	IEC 60297-3-100, IEC 60297-3-101, IEEE 1101.1	否	插箱/机箱	84 HP	7.5 kgf
24564-432	机架	IEC 60297-3-100, IEC 60297-3-101, IEEE 1101.1	否	插箱/机箱	84 HP	7.5 kgf
24564-431	机架	IEC 60297-3-100, IEC 60297-3-101, IEEE 1101.1	否	插箱/机箱	84 HP	7.5 kgf
24564-133	机架	IEC 60297-3-100, IEC 60297-3-101, IEEE 1101.1	否	插箱/机箱	84 HP	7.5 kgf

物料号	安装	符合	EMC 屏蔽	产品类型	机架宽度	静态负载
24564-132	机架	IEC 60297-3-100, IEC 60297-3-101, IEEE 1101.1	否	插箱/机箱	84 HP	7.5 kgf
24564-131	机架	IEC 60297-3-100, IEC 60297-3-101, IEEE 1101.1	否	插箱/机箱	84 HP	7.5 kgf

其他产品详情

Subrack is not prepared for shielding, retrofit for protection class IP 20 possible

Individual configuration: broad range of variants in height, width and depth; guide rails for a wide variety of applications; interior options; accessories and mounting material.

警告

应仅根据 nVent 的产品说明书与培训材料安装并使用 nVent 的产品。可访问 www.nvent.com 获取说明书，或者向您的 nVent 客服代表索取。错误安装、使用不当、滥用或未能完全遵守 nVent 的说明与警告，可能会造成产品故障、财产损失、严重的人身伤害及死亡和/或使得保修服务无效。



我们强大的品牌组合:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE