


EuropacPRO 19" Subrack Kit for Backplane, Shielded

电力公用事业

用于背板安装的 EMC 屏蔽插箱，后侧由后面板覆盖。



认证



功能

Subrack with side panel type F ("flexible"), front 19" bracket included, depth-adjustable 19" bracket sold separately (not included in items delivered)

扁平包装，节省空间

提供改制，如开孔、各种表面或尺寸

EMC of approximately 40 dB at 1 GHz, 30 dB at 2 GHz, assuming that the front is covered with shielded front panels, testing in accordance with VG 95373 part 15

IP 20, in accordance with IEC 60529

铝结构

内部和外部尺寸符合：IEC 60297-3-100, -101, IEEE 1101.1

用于安装背板的后水平横梁，带绝缘条

技术参数

产品类型: 插箱/机箱

Table 1/2						
物料号	机架高度	深度	包装数量	用于安装	板深度	EMC 垫片类型
24563-142	3 U	235 mm	1	背板	160 mm, 220 mm	泡棉
24563-143	3 U	295 mm	1	背板	160 mm, 220 mm, 280 mm	泡棉
24563-144	3 U	355 mm	1	背板	160 mm, 220 mm, 280 mm	泡棉
24563-145	3 U	415 mm	1	背板	160 mm, 220 mm, 280 mm	泡棉
24563-146	3 U	475 mm	1	背板	160 mm, 220 mm, 280 mm	泡棉
24563-442	6 U	235 mm	1	背板	160 mm, 220 mm	泡棉
24563-443	6 U	295 mm	1	背板	160 mm, 220 mm, 280 mm	泡棉
24563-444	6 U	355 mm	1	背板	160 mm, 220 mm, 280 mm	泡棉
24563-445	6 U	415 mm	1	背板	160 mm, 220 mm, 280 mm	泡棉
24563-446	6 U	475 mm	1	背板	160 mm, 220 mm, 280 mm	泡棉

Table 2/2						
物料号	包含把手	安装	符合	EMC 屏蔽	机架宽度	静态负载
24563-142	否	机架	IEC 60297-3-103	是	84 HP	11 kgf
24563-143	否	机架	IEC 60297-3-103	是	84 HP	11 kgf

物料号	包含把手	安装	符合	EMC 屏蔽	机架宽度	静态负载
24563-144	否	机架	IEC 60297-3-103	是	84 HP	11 kgf
24563-145	否	机架	IEC 60297-3-103	是	84 HP	11 kgf
24563-146	否	机架	IEC 60297-3-103	是	84 HP	11 kgf
24563-442	否	机架	IEC 60297-3-103	是	84 HP	11 kgf
24563-443	否	机架	IEC 60297-3-103	是	84 HP	11 kgf
24563-444	否	机架	IEC 60297-3-103	是	84 HP	11 kgf
24563-445	否	机架	IEC 60297-3-103	是	84 HP	11 kgf
24563-446	否	机架	IEC 60297-3-103	是	84 HP	11 kgf

ADDITIONAL PRODUCT DETAILS

单个配置：支持大范围高度、宽度和深度；根据不同应用可选多种规格导轨；内部选项；附件和安装材料。

警告

应仅根据 nVent 的产品说明书与培训材料安装并使用 nVent 的产品。可访问 www.nvent.com 获取说明书，或者向您的 nVent 客服代表索取。错误安装、使用不当、滥用或未能完全遵守 nVent 的说明与警告，可能会造成产品故障、财产损失、严重的人身伤害及死亡和/或使得保修服务无效。



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE