

Interscale 19" Rack Mount Chassis, Non-Perforated

电力公用事业



Flexible 19" Chassis with integrated EMC protection. Based on the nVent SCHROFF Interscale platform and developed in accordance with IEC 60297-3-109.

认证



功能

Modular desktop case consisting of 4 assembled parts

Developed according to IEC 60297-3-109 (under progress at IEC)

集成 EMC 屏蔽

Ingress protection up to IP 30

Color RAL 7016

Modified or customized cases available upon request

技术参数

Table 1/2						
物料号	机架高度	深度	包装数量	可用宽度	安装	符合
14821-105	1 U	221.45 mm	1	443.7 mm	机架	IEC 60297-3-100, IEC 60297-3-109
14821-107	1 U	310.35 mm	1	443.7 mm	机架	IEC 60297-3-100, IEC 60297-3-109
14821-205	2 U	221.45 mm	1	443.7 mm	机架	IEC 60297-3-100, IEC 60297-3-109
14821-207	2 U	310.35 mm	1	443.7 mm	机架	IEC 60297-3-100, IEC 60297-3-109
14821-305	3 U	221.45 mm	1	443.7 mm	机架	IEC 60297-3-100, IEC 60297-3-109
14821-307	3 U	310.35 mm	1	443.7 mm	机架	IEC 60297-3-100, IEC 60297-3-109

Table 2/2				
物料号	EMC 屏蔽	产品系列	产品类型	类型
14821-105	是	Interscale	小尺寸机箱	实心导线
14821-107	是	Interscale	小尺寸机箱	实心导线
14821-205	是	Interscale	小尺寸机箱	实心导线
14821-207	是	Interscale	小尺寸机箱	实心导线
14821-305	是	Interscale	小尺寸机箱	实心导线
14821-307	是	Interscale	小尺寸机箱	实心导线

警告

应仅根据 nVent 的产品说明书与培训材料安装并使用 nVent 的产品。可访问 www.nvent.com 获取说明书，或者向您的 nVent 客服代表索取。错误安装、使用不当、滥用或未能完全遵守 nVent 的说明与警告，可能会造成产品故障、财产损失、严重的人身伤害及死亡和/或使得保修服务无效。



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE