

MBJYG Grounding and Bonding Braid, Tinned Copper, Halogen Free

Power Utilities



MBJYG Grounding and Bonding Braids are a reliable and convenient ground solution for applications that require flexibility and durability. Designed with halogen-free and flame retardant yellow green insulation, MBJYG braids are made with tinned copper ground braids and solid palms that are ready to install without any additional cutting, stripping, crimping or punching. MBJYG braids also do not require the addition of tin or crimped lugs and the proprietary manufacturing process helps optimize the electrical contact between each wire and helps eliminate moisture issues in the palms, helping prevent corrosion and extend the useful life of the braid.

认证









功能

Complete range of earth/ground flexible connections from $6 - 25 \text{ mm}^2$ (11.84 - 49.33 kcmil) cross section and from 100 - 300 mm (3.937" - 11.811") length

Integral palm, without tin or crimped lugs for superior electrical contact and tensile strength resistance

Resistant to vibration and fatigue, reducing maintenance

Provides weight savings, material savings and lower impedance when compared to similar lugged cables with insulation

Ready to use out of the box, eliminates the need for cutting, stripping, crimping and punching

Halogen free and flame retardant yellow green insulation

Quick and easy to install

Recommended by the EMC/EMI directives and less impedance than cables

RoHS compliant

技术参数

Table 1/2									
物料号	订货号	介电强度	无卤素等级	标称电压,UL/ CSA/IEC	工作温度	安培容量			
MBJYG10-100-	563606	15 kV/mm	EN 14582	600 V	-55 to 125 °C	75 A			

Table 2/2									
物料号	订货号	厚度 (T)	A	В	单位重量				
MBJYG10-100-6	563606	1.10 mm	11 mm	18 mm	0.012 kg				

警告

应仅根据 nVent 的产品说明书与培训材料安装并使用 nVent 的产品。可访问 www.nvent.com 获取说明书,或者向您的 nVent 客服代表索取。错误安装、使用不当、滥用或未能完全遵守 nVent

的说明与警告,可能会造成产品故障、财产损失、严重的人身伤害及死亡和/或使得保修服务无效。



我们强大的品牌组合:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE

本文档由系统生成。 nVent.com 3