


RatiopacPRO AIR 19" Rack Mount Case, Retrofittable Shielding With Handles

电力公用事业



nVent SCHROFF RatiopacPRO 仪器箱可为 19" 和单个电子组件提供电子保护。这种灵活、可靠的仪器箱可轻松从台式转换为 19"

机架安装仪器箱，包含四种不同的选项。此版本的机箱配有高级散热功能和带把手的安装支架，用于装配在 19" 机架中。

认证



功能

Cases for individual assembly with 19" standard components or specific internal mounting, e.g. with mounting plate

可加装EMC 屏蔽组件

Version with 19" mounting brackets with front handles, no visible screws

The case has 2 x 1/2 U clearances for ventilation beneath and above the board cage

For board depth 160 mm, 220 mm, 280 mm, and 340 mm (depending on case depth)

对称设计，正面和背面完全相同

Conforms with DIN EN 62368-1

Table 1/3						
物料号	机架高度	深度	包装数量	可用高度	可用宽度	前部框架结构
24572-670	3 U	255.5 mm	1	112.3 mm	432 mm	19" Mounting Brackets with Handles, Horizontal Rails
24572-673	3 U	315.5 mm	1	112.3 mm	432 mm	19" Mounting Brackets with Handles, Horizontal Rails
24572-674	3 U	375.5 mm	1	112.3 mm	432 mm	19" Mounting Brackets with Handles, Horizontal Rails
24572-675	3 U	435.5 mm	1	112.3 mm	432 mm	19" Mounting Brackets with Handles, Horizontal Rails
24572-676	3 U	495.5 mm	1	112.3 mm	432 mm	19" Mounting Brackets with Handles, Horizontal Rails
24572-690	6 U	255.5 mm	1	245.7 mm	432 mm	19" Mounting Brackets with Handles, Horizontal Rails
24572-693	6 U	315.5 mm	1	245.7 mm	432 mm	19" Mounting Brackets with Handles, Horizontal Rails

物料号	机架高度	深度	包装数量	可用高度	可用宽度	前部框架结构
24572-694	6 U	375.5 mm	1	245.7 mm	432 mm	19" Mounting Brackets with Handles, Horizontal Rails
24572-695	6 U	435.5 mm	1	245.7 mm	432 mm	19" Mounting Brackets with Handles, Horizontal Rails
24572-696	6 U	495.5 mm	1	245.7 mm	432 mm	19" Mounting Brackets with Handles, Horizontal Rails

Table 2/3

物料号	制冷选项	符合	EMC 屏蔽	高度	产品系列	产品类型
24572-670	是	IEC 60297-3-101, IEC 60297-3-102, IEEE 1101.1, IEEE 1101.10, IEEE 1101.11	无 (支持升级)	177 mm	RatiopacPRO AIR	机箱
24572-673	是	IEC 60297-3-101, IEC 60297-3-102, IEEE 1101.1, IEEE 1101.10, IEEE 1101.11	无 (支持升级)	177 mm	RatiopacPRO AIR	机箱
24572-674	是	IEC 60297-3-101, IEC 60297-3-102, IEEE 1101.1, IEEE 1101.10, IEEE 1101.11	无 (支持升级)	177 mm	RatiopacPRO AIR	机箱

物料号	制冷选项	符合	EMC 屏蔽	高度	产品系列	产品类型
24572-675	是	IEC 60297-3-101, IEC 60297-3-102, IEEE 1101.1, IEEE 1101.10, IEEE 1101.11	无 (支持升级)	177 mm	RatiopacPRO AIR	机箱
24572-676	是	IEC 60297-3-101, IEC 60297-3-102, IEEE 1101.1, IEEE 1101.10, IEEE 1101.11	无 (支持升级)	177 mm	RatiopacPRO AIR	机箱
24572-690	是	IEC 60297-3-101, IEC 60297-3-102, IEEE 1101.1, IEEE 1101.10, IEEE 1101.11	无 (支持升级)	310.35 mm	RatiopacPRO AIR	机箱
24572-693	是	IEC 60297-3-101, IEC 60297-3-102, IEEE 1101.1, IEEE 1101.10, IEEE 1101.11	无 (支持升级)	310.35 mm	RatiopacPRO AIR	机箱
24572-694	是	IEC 60297-3-101, IEC 60297-3-102, IEEE 1101.1, IEEE 1101.10, IEEE 1101.11	无 (支持升级)	310.35 mm	RatiopacPRO AIR	机箱
24572-695	是	IEC 60297-3-101, IEC 60297-3-102, IEEE 1101.1, IEEE 1101.10, IEEE 1101.11	无 (支持升级)	310.35 mm	RatiopacPRO AIR	机箱

物料号	制冷选项	符合	EMC 屏蔽	高度	产品系列	产品类型
24572-696	是	IEC 60297-3-101, IEC 60297-3-102, IEEE 1101.1, IEEE 1101.10, IEEE 1101.11	无 (支持升级)	310.35 mm	RatiopacPRO AIR	机箱

Table 3/3					
物料号	防护等级	机架宽度	静态负载	类型	宽度
24572-670	IP20	84 HP	25 kgf	用于安装单个电子器件的仪器箱	448.9 mm
24572-673	IP20	84 HP	25 kgf	用于安装单个电子器件的仪器箱	448.9 mm
24572-674	IP20	84 HP	25 kgf	用于安装单个电子器件的仪器箱	448.9 mm
24572-675	IP20	84 HP	25 kgf	用于安装单个电子器件的仪器箱	448.9 mm
24572-676	IP20	84 HP	25 kgf	用于安装单个电子器件的仪器箱	448.9 mm
24572-690	IP20	84 HP	25 kgf	用于安装单个电子器件的仪器箱	448.9 mm
24572-693	IP20	84 HP	25 kgf	用于安装单个电子器件的仪器箱	448.9 mm
24572-694	IP20	84 HP	25 kgf	用于安装单个电子器件的仪器箱	448.9 mm
24572-695	IP20	84 HP	25 kgf	用于安装单个电子器件的仪器箱	448.9 mm
24572-696	IP20	84 HP	25 kgf	用于安装单个电子器件的仪器箱	448.9 mm

ADDITIONAL PRODUCT DETAILS

- 可定制（特殊颜色或尺寸）。
- 定制解决方案（支持顶盖、底板或侧板开孔）。
- 提供装配服务，一件起售。

警告

应仅根据 nVent 的产品说明书与培训材料安装并使用 nVent 的产品。可访问 www.nvent.com 获取说明书，或者向您的 nVent 客服代表索取。错误安装、使用不当、滥用或未能完全遵守 nVent 的说明与警告，可能会造成产品故障、财产损失、严重的人身伤害及死亡和/或使得保修服务无效。



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE