

Varistar CP Deco Cabinet With 19" Panel Mounts in Deco Frame

Power Utilities

Varistar: Highly versatile, robust welded steel frame electronics cabinet with a wide range of available features including protection against dust and water (IP 20 and IP 55), cooling options from fans to 40kW air-to-water chillers, shock, vibration and seismic resistance up to NEBS GR-63-CORE Bellcore zone 4 and industry leading radio-frequency/electromagnetic (RFI / EMI) shielding of 60 dB at 1 GHz, 40 dB at 3 GHz (tested to IEC 61587-3).

功能

Open at front (no door)

19" panel mounts integrated into decoration frame

Rear door with single point locking, side panels with quick release fastener

Static load - carrying capacity 400 kg (mounted at decoration frame)

技术参数

Table 1/3

物料号	机架高度	高度	框架颜色	宽度	框架颜色代码	覆层材料
10630-034	38 U	1800 mm	暗灰色	600 mm	RAL 7021	钢
10630-033	38 U	1800 mm	暗灰色	600 mm	RAL 7021	钢
10630-035	42 U	2000 mm	暗灰色	600 mm	RAL 7021	钢

物料号	机架高度	高度	框架颜色	宽度	框架颜色代码	覆层材料
10630-036	42 U	2000 mm	暗灰色	600 mm	RAL 7021	钢

Table 2/3						
物料号	深度	覆层颜色	覆层颜色代码	符合	框架材料	产品类型
10630-034	800 mm	暗灰色	RAL 7021	IEC 60297-3-100	钢	机柜
10630-033	600 mm	暗灰色	RAL 7021	IEC 60297-3-100	钢	机柜
10630-035	600 mm	暗灰色	RAL 7021	IEC 60297-3-100	钢	机柜
10630-036	800 mm	暗灰色	RAL 7021	IEC 60297-3-100	钢	机柜

Table 3/3	
物料号	静态负载
10630-034	400 kgf
10630-033	400 kgf
10630-035	400 kgf
10630-036	400 kgf

其他产品详情

Lever handle can be added to rear door.

Further dimensions and version available on ServicePlus EMC. Please order base/plinth separately. For assembly of shelves and slide rails another pair of panel/slide mounts is necessary.

警告

应仅根据 nVent 的产品说明书与培训材料安装并使用 nVent 的产品。可访问 www.nvent.com 获取说明书，或者向您的 nVent 客服代表索取。错误安装、使用不当、滥用或未能完全遵守 nVent 的说明与警告，可能会造成产品故障、财产损失、严重的人身伤害及死亡和/或使得保修服务无效。



我们强大的品牌组合:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE