

Varistar CP Glazed Door With 3-Point Locking

Power Utilities

Glass door with 3 point locking allows stronger adhesion between door and the cabinet frame. This prevents the metal malleability to show and provides the door extra robustness.

功能

Glazed Door With 3-Point Locking, With Lock

Lever handle with key insert (2 keys)

Opening angle 180°

Security glass, 6 mm

Standard fitting, lock on right-hand door

Can be retrofitted with lever handle 24630003 and DIN profile half cylinder with keys or push button

技术参数

Table 1/3

物料号	机架高度	高度	宽度	防护等级	颜色	颜色代码
21630-092	42 U	2000 mm	600 mm	IP20	暗灰色	RAL 7021
21630-093	47 U	2200 mm	600 mm	IP20	暗灰色	RAL 7021
21630-094	52 U	2450 mm	600 mm	IP20	暗灰色	RAL 7021
21630-095	42 U	2000 mm	800 mm	IP20	暗灰色	RAL 7021

物料号	机架高度	高度	宽度	防护等级	颜色	颜色代码
21630-096	47 U	2200 mm	800 mm	IP20	暗灰色	RAL 7021
21630-097	52 U	2450 mm	800 mm	IP20	暗灰色	RAL 7021
21630-416	24 U	1200 mm	600 mm	IP20	暗灰色	RAL 7021
21630-417	24 U	1200 mm	800 mm	IP20	暗灰色	RAL 7021
21630-418	29 U	1400 mm	600 mm	IP20	暗灰色	RAL 7021
21630-419	29 U	1400 mm	800 mm	IP20	暗灰色	RAL 7021
21630-420	33 U	1600 mm	600 mm	IP20	暗灰色	RAL 7021
21630-421	33 U	1600 mm	800 mm	IP20	暗灰色	RAL 7021
21630-422	38 U	1800 mm	600 mm	IP20	暗灰色	RAL 7021
21630-423	38 U	1800 mm	800 mm	IP20	暗灰色	RAL 7021
21630-717	24 U	1200 mm	600 mm	IP55	暗灰色	RAL 7021
21630-718	24 U	1200 mm	800 mm	IP55	暗灰色	RAL 7021
21630-719	29 U	1400 mm	600 mm	IP55	暗灰色	RAL 7021
21630-720	29 U	1400 mm	800 mm	IP55	暗灰色	RAL 7021
21630-721	33 U	1600 mm	600 mm	IP55	暗灰色	RAL 7021
21630-722	33 U	1600 mm	800 mm	IP55	暗灰色	RAL 7021
21630-723	38 U	1800 mm	600 mm	IP55	暗灰色	RAL 7021

物料号	机架高度	高度	宽度	防护等级	颜色	颜色代码
21630-724	38 U	1800 mm	800 mm	IP55	暗灰色	RAL 7021
21630-725	42 U	2000 mm	600 mm	IP55	暗灰色	RAL 7021
21630-726	42 U	2000 mm	800 mm	IP55	暗灰色	RAL 7021
21630-727	47 U	2200 mm	600 mm	IP55	暗灰色	RAL 7021
21630-728	47 U	2200 mm	800 mm	IP55	暗灰色	RAL 7021

Table 2/3						
物料号	符合	完成	锁定类型	材料	产品类型	类型
21630-092	IEC 61587-1, IEC 61587-3		3 点锁定		机柜门	玻璃门
21630-093	IEC 61587-1, IEC 61587-3		3 点锁定		机柜门	玻璃门
21630-094	IEC 61587-1, IEC 61587-3		3 点锁定		机柜门	玻璃门
21630-095	IEC 61587-1, IEC 61587-3		3 点锁定		机柜门	玻璃门
21630-096	IEC 61587-1, IEC 61587-3		3 点锁定		机柜门	玻璃门
21630-097	IEC 61587-1, IEC 61587-3		3 点锁定		机柜门	玻璃门
21630-416	IEC 61587-1, IEC 61587-3		3 点锁定		机柜门	玻璃门
21630-417	IEC 61587-1, IEC 61587-3		3 点锁定		机柜门	玻璃门
21630-418	IEC 61587-1, IEC 61587-3		3 点锁定		机柜门	玻璃门
21630-419	IEC 61587-1, IEC 61587-3		3 点锁定		机柜门	玻璃门

物料号	符合	完成	锁定类型	材料	产品类型	类型
21630-420	IEC 61587-1, IEC 61587-3		3 点锁定		机柜门	玻璃门
21630-421	IEC 61587-1, IEC 61587-3		3 点锁定		机柜门	玻璃门
21630-422	IEC 61587-1, IEC 61587-3		3 点锁定		机柜门	玻璃门
21630-423	IEC 61587-1, IEC 61587-3		3 点锁定		机柜门	玻璃门
21630-717	IEC 61587-1	粉末涂层	3 点锁定	钢, 玻璃	机柜门	玻璃门
21630-718	IEC 61587-1	粉末涂层	3 点锁定	钢, 玻璃	机柜门	玻璃门
21630-719	IEC 61587-1	粉末涂层	3 点锁定	钢, 玻璃	机柜门	玻璃门
21630-720	IEC 61587-1	粉末涂层	3 点锁定	钢, 玻璃	机柜门	玻璃门
21630-721	IEC 61587-1	粉末涂层	3 点锁定	钢, 玻璃	机柜门	玻璃门
21630-722	IEC 61587-1	粉末涂层	3 点锁定	钢, 玻璃	机柜门	玻璃门
21630-723	IEC 61587-1	粉末涂层	3 点锁定	钢, 玻璃	机柜门	玻璃门
21630-724	IEC 61587-1	粉末涂层	3 点锁定	钢, 玻璃	机柜门	玻璃门
21630-725	IEC 61587-1	粉末涂层	3 点锁定	钢, 玻璃	机柜门	玻璃门
21630-726	IEC 61587-1	粉末涂层	3 点锁定	钢, 玻璃	机柜门	玻璃门
21630-727	IEC 61587-1	粉末涂层	3 点锁定	钢, 玻璃	机柜门	玻璃门
21630-728	IEC 61587-1	粉末涂层	3 点锁定	钢, 玻璃	机柜门	玻璃门

Table 3/3

物料号	搭配
21630-092	Varistar CP
21630-093	Varistar CP
21630-094	Varistar CP
21630-095	Varistar CP
21630-096	Varistar CP
21630-097	Varistar CP
21630-416	Varistar CP
21630-417	Varistar CP
21630-418	Varistar CP
21630-419	Varistar CP
21630-420	Varistar CP
21630-421	Varistar CP
21630-422	Varistar CP
21630-423	Varistar CP
21630-717	Varistar CP
21630-718	Varistar CP

物料号	搭配
21630-719	Varistar CP
21630-720	Varistar CP
21630-721	Varistar CP
21630-722	Varistar CP
21630-723	Varistar CP
21630-724	Varistar CP
21630-725	Varistar CP
21630-726	Varistar CP
21630-727	Varistar CP
21630-728	Varistar CP

其他产品详情

Please order DIN profile half cylinder for lever handle 24630003 separately.

Please purchase the grounding kit separately.

警告

应仅根据 nVent 的产品说明书与培训材料安装并使用 nVent 的产品。可访问 www.nvent.com 获取说明书，或者向您的 nVent 客服代表索取。错误安装、使用不当、滥用或未能完全遵守 nVent 的说明与警告，可能会造成产品故障、财产损失、严重的人身伤害及死亡和/或使得保修服务无效。



我们强大的品牌组合:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE