

E650C-R Gutter Sensor for Elexant 650c-Modbus



Rod-shaped sensor E650C-R for combined measurement of temperature and moisture values in gutters and neighbouring areas, such as flat roofs and downpipes to be used with Elexant 650c-Modbus. Robust version made of brass, fully encapsulated. Extremely compact design with axial cable outlet and threaded bolt for fixing in position. Optional mounting plate for sensor E650C-R can be used with sensor height adjustment above the mounting surface. The mounting plate can be matched to the mounting location by bending and then attached by gluing or soldering. Two material versions are available for suitable material combinations in gutter and flat roof applications.

功能

Cable connection: 轴流

Connection cable: 4 x 0.5 mm²

Temperature range for moisture measurement: -20°C to 30°C

技术参数

Table 1/2

物料号	通信	深度	危险区域	高度	IP 等级	测量范围
1244-022798	否	80 mm	否	2 mm	IP68	
1244-022799	否	80 mm	否	2 mm	IP68	
1244-022795	否	96 mm	否	14 mm	IP68	-20 to 30 °C

Table 2/2

物料号	宽度
1244-022798	132 mm
1244-022799	132 mm
1244-022795	14 mm

警告

应仅根据 nVent 的产品说明书与培训材料安装并使用 nVent 的产品。可访问 www.nvent.com 获取说明书，或者向您的 nVent 客服代表索取。错误安装、使用不当、滥用或未能完全遵守 nVent 的说明与警告，可能会造成产品故障、财产损失、严重的人身伤害及死亡和/或使得保修服务无效。

北美

Tel +1.800.545.6258

Fax +1.800.527.5703

thermal.info@nvent.com

Europe, Middle East,

Africa

Tel +32.16.213.511

Fax +32.16.213.604

thermal.info@nvent.com

亚太地区

Tel +86.21.2412.1688

Fax +86.21.5426.3167

cn.thermal.info@nvent.com

拉丁美洲

Tel +1.713.868.4800

Fax +1.713.868.2333

thermal.info@nvent.com

Our powerful portfolio of brands:

RAYCHEM PYROTENAX TRACER NUHEAT