

Elexant 5010i Field Controller



nVent RAYCHEM Elexant 5010i is an advanced field-mountable electronic temperature controller providing local control and central monitoring capabilities, used for single phase circuits up to 25 A and suitable for hazardous areas. The Elexant 5010i-LIM is provided with an integrated digital intelligent safety temperature limiter (SIL 2 device).

功能

Easy to install, program and operate

Remote configuration and monitoring through the user interfaces TOUCH 1500 and NGC-UIT3, or via the nVent RAYCHEM Supervisor software

Local monitoring and configuration by using the hand-held wireless tablet

Extensive control, monitoring and alarm capabilities

Automated system check, reduces unexpected and expensive downtime of important pipelines

Alarm relay, RS-485 Modbus communication

技术参数

额定电流:	25 A
额定电压:	100 – 250 V
高度:	120 mm
宽度:	220 mm
控制器温度设置:	–200 to 700 °C
工作温度:	–50 to 60 °C

Table 1/1

物料号	项目名称	包含限制器
2000002133	Elexant 5010i-LIM	是

物料号	项目名称	包含限制器
2000002370	Elexant 5010i (EAC)	否
2000002132	Elexant 5010i	否
2000002369	Elexant 5010i-LIM (EAC)	是

警告

应仅根据 nVent 的产品说明书与培训材料安装并使用 nVent 的产品。可访问 www.nvent.com 获取说明书，或者向您的 nVent 客服代表索取。错误安装、使用不当、滥用或未能完全遵守 nVent 的说明与警告，可能会造成产品故障、财产损失、严重的人身伤害及死亡和/或使得保修服务无效。

North America

Tel +1.800.545.6258
Fax +1.800.527.5703
thermal.info@nvent.com

Europe, Middle East, Africa

Tel +32.16.213.511
Fax +32.16.213.604
thermal.info@nvent.com

Asia Pacific

Tel +86.21.2412.1688
Fax +86.21.5426.3167
cn.thermal.info@nvent.com

Latin America

Tel +1.713.868.4800
Fax +1.713.868.2333
thermal.info@nvent.com

我们强大的品牌组合:

RAYCHEM PYROTENAX TRACER NUHEAT