

EMDR-10 控制装置



This product is currently being phased out, to be replaced by the all-new Elexant 650c-Modbus. nVent RAYCHEM EMDR-10 is an energy efficient controller for Icestop GM-2X/T self-regulating roof and gutter de-icing systems.

配备温度和湿度传感器，只有在同时检测到低温和湿气时，系统才会激活。

功能

安装和操作简单快速

节能，只有在检测到寒冷天气和湿气时，电路才会通电

使用寿命长，安全可靠：6 year product warranty available, maintenance free

技术参数

Table 1/3

物料号	项目名称	额定电压	额定频率	Adjustment Range, Frost Protection	Nominal Switching Current @ 250V, Potential Free	传感器类型
449554-000	EMDR-10	230 V	50 Hz min	-3 to 6 °C	1 A	PTC

Table 2/3

物料号	项目名称	湿度传感器	环境传感器	Power Consumption, Standby	IP 等级	高度
449554-000	EMDR-10	是	是	4 W	IP20	90 mm

Table 3/3				
物料号	项目名称	宽度	深度	最短温度相
449554-000	EMDR-10	110 mm	58 mm	1（最小值）

警告

应仅根据 nVent 的产品说明书与培训材料安装并使用 nVent 的产品。可访问 www.nvent.com 获取说明书，或者向您的 nVent 客服代表索取。错误安装、使用不当、滥用或未能完全遵守 nVent 的说明与警告，可能会造成产品故障、财产损失、严重的人身伤害及死亡和/或使得保修服务无效。

北美	Europe, Middle East, Africa	亚太地区	拉丁美洲
Tel +1.800.545.6258	Tel +32.16.213.511	Tel +86.21.2412.1688	Tel +1.713.868.4800
Fax +1.800.527.5703	Fax +32.16.213.604	Fax +86.21.5426.3167	Fax +1.713.868.2333
thermal.info@nvent.com	thermal.info@nvent.com	cn.thermal.info@nvent.com	thermal.info@nvent.com