

NRG-DM Digital Timer Thermostat



nVent RAYCHEM NRG-DM is a digital timer thermostat for electrical floor heating equipped with a large display and intuitive software. Eco Design compliant thanks to the following functions: Adaptive start control. For more details, please consult the Commissioning sheet (INST324 or EU2550).

功能

Easy to use, intuitive navigation: large LCD display with blue back light

3 operating modes: event mode or weekly schedule to reduce energy; boost mode or temporary override; constant mode

Energy efficient adaptive function

Optimum heat management, with 4 sensor modes

使用寿命长，安全可靠：12 year total care warranty available, maintenance free

技术参数

Table 1/5

物料号	项目名称	电源	测量范围	Adjustable Differential	Regulation Type	Max Contact Voltage
1244-015152	R-NRG-DM	230 V	5 – 40 °C	否	开/关	230 V

Table 2/5

物料号	项目名称	最大触点负载	Sensor/Feeler Type	Temperature Control Class	Control Characteristic	Remote Operation
1244-015152	R-NRG-DM	13 A	Resistance Sensor	IV	PID	否

Table 3/5						
物料号	项目名称	Switching Program Quantity	Power Consumption, Standby	IP 等级	RAL Number	颜色
1244-015152	R-NRG-DM	7	0.4 W	IP21	9010	Clear White

Table 4/5						
物料号	项目名称	IFTTT Support Available	Clock Type	Clock Model	Self Learning	高度
1244-015152	R-NRG-DM	否	Day Clock	数字化	是	82 mm

Table 5/5			
物料号	项目名称	宽度	深度
1244-015152	R-NRG-DM	82 mm	40 mm

警告

应仅根据 nVent 的产品说明书与培训材料安装并使用 nVent 的产品。可访问 www.nvent.com 获取说明书，或者向您的 nVent 客服代表索取。错误安装、使用不当、滥用或未能完全遵守 nVent 的说明与警告，可能会造成产品故障、财产损失、严重的人身伤害及死亡和/或使得保修服务无效。

北美

Tel +1.800.545.6258

Fax +1.800.527.5703

thermal.info@nvent.com

Europe, Middle East,

Africa

Tel +32.16.213.511

Fax +32.16.213.604

thermal.info@nvent.com

亚太地区

Tel +86.21.2412.1688

Fax +86.21.5426.3167

cn.thermal.info@nvent.com

拉丁美洲

Tel +1.713.868.4800

Fax +1.713.868.2333

thermal.info@nvent.com

Our powerful portfolio of brands:

RAYCHEM PYROTENAX TRACER NUHEAT