

适用 19" 风扇盘的 1 U 导风板

1 U

高的导风板，用于引导空气从正面流向顶部，或从底部流向背面。



认证



功能

装配选项：– 一个风扇盘：从前部向上抽吸冷空气 – 两个风扇盘：从前部抽吸冷空气, 向上抽吸并导流到后部（参阅应用图）

如安装 19" 风扇盘，冷却能力更佳

通过改变气流方向避免热量垂直积聚

可选过滤垫, 方便现场更换

技术参数

Table 1/1

物料号	搭配	完成	材料	包装数量	快速发货
10713-151	19" 风扇盘	粉末涂层	钢	1	No
10713-147	19" 风扇盘	粉末涂层	钢	1	No
10713-148	19" 风扇盘	粉末涂层	钢	1	No

物料号	搭配	完成	材料	包装数量	快速发货
10713-141	19" 风扇盘	粉末涂层	钢	1	No
10713-142	19" 风扇盘	粉末涂层	钢	1	No
10713-146	19" 风扇盘	粉末涂层	钢	1	No
10713-149	19" 风扇盘	粉末涂层	钢	1	No
10713-145	19" 风扇盘	粉末涂层	钢	1	No
10713-140	19" 风扇盘	粉末涂层	钢	1	No
10713-150	19" 风扇盘	粉末涂层	钢	1	No
10713-143	19" 风扇盘	粉末涂层	钢	1	No
10713-144	19" 风扇盘	粉末涂层	钢	1	No

North America
All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe
Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia
Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India
Dubai, United Arab
Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



我们强大的品牌组合:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE