

19" 设备架, 深度可调

SCHROFF 19" 层板的承载能力为 10 Kg, 有助于机架管理人员将关键设备放在机柜内。



认证



功能

深度可调, 以 25 mm为网格增量, 前向突出至少 26 mm

安装高度 2 U

静态承载能力 15 千克

技术参数

产品类型: 货架

材料: 钢

Table 1/2

物料号	宽度	深度	包装数量	颜色	颜色代码	完成
20118-786	430mm	250mm	1	暗灰色	RAL 7021	粉末涂层
20118-791	430mm	400mm	1	浅灰色	RAL 7035	粉末涂层

物料号	宽度	深度	包装数量	颜色	颜色代码	完成
20118-790	430mm	300mm	1	浅灰色	RAL 7035	粉末涂层
20118-789	430mm	250mm	1	浅灰色	RAL 7035	粉末涂层
20118-788	430mm	400mm	1	暗灰色	RAL 7021	粉末涂层
20118-787	430mm	300mm	1	暗灰色	RAL 7021	粉末涂层

Table 2/2		
物料号	类型	快速发货
20118-786	设备机架	No
20118-791	设备机架	No
20118-790	设备机架	No
20118-789	设备机架	No
20118-788	设备机架	No
20118-787	设备机架	No

警告

应仅根据 nVent 的产品说明书与培训材料安装并使用 nVent 的产品。可访问 www.nvent.com 获取说明书，或者向您的 nVent 客服代表索取。错误安装、使用不当、滥用或未能完全遵守 nVent 的说明与警告，可能会造成产品故障、财产损失、严重的人身伤害及死亡和/或使得保修服务无效。

North America

All locations

+1.763.422.2661

Chat with us:

nvent.com/schroff

Europe

Straubenhardt, Germany

+49.7082.794.0

Betschdorf, France

+33.3.88.90.64.90

Warsaw, Poland

+48.22.209.98.35

Assago, Italy

+39.02.932.7141

Chat with us:

nvent.com/schroff

Asia

Shanghai, China

+86.21.2412.6943

Qingdao, China

+86.532.8771.6101

Singapore

+65.6768.5800

Shin-Yokohama, Japan

+81.45.476.0271

Chat with us:

nvent.com/schroff

Middle East & India

Dubai, United Arab

Emirates

+971.4.378.1700

Bangalore, India

+91.80.6715.2001

Istanbul, Turkey

+90.216.250.7374

Chat with us:

nvent.com/schroff



我们强大的品牌组合:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE