

19" 设备架

深度可调的 19" 设备架，承载能力为 15kg。



认证



功能

安装高度 2 U

承载能力 15 千克

深度可调，以 25 mm为增量, 向前突出至少 91 mm, 最多 191 mm

技术参数

产品类型: 电缆托盘

材料: 钢

Table 1/2

物料号	宽度	深度	包装数量	颜色	颜色代码	完成
20118-794	430mm	450mm	1	浅灰色	RAL 7035	粉末涂层
20118-795	430mm	450mm	1	暗灰色	RAL 7021	粉末涂层

Table 2/2		
物料号	类型	快速发货
20118-794	设备机架	No
20118-795	设备机架	No

警告

应仅根据 nVent 的产品说明书与培训材料安装并使用 nVent 的产品。可访问 www.nvent.com 获取说明书，或者向您的 nVent 客服代表索取。错误安装、使用不当、滥用或未能完全遵守 nVent 的说明与警告，可能会造成产品故障、财产损失、严重的人身伤害及死亡和/或使得保修服务无效。

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab
Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



我们强大的品牌组合:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE