

19" 风扇单元, 1 U, 前面板带开关

交流设备上的前装式发光电源开关，带额外的后部电源插座；适用于电源输入和电源输出电缆的机械应力消除装置。



认证



功能

可根据插箱规格进行调整

符合 DIN EN ISO 13857 标准的接触保护

技术参数

Table 1/1

物料号	交流输入电压	直流输入电压	包装数量	完成	材料	快速发货
10713-108	230V min		1	镀锌铝, 阳极氧化	钢, 铝	No
10713-112	230V		1	镀锌铝, 阳极氧化	钢, 铝	No
10713-114	115V		1	镀锌铝, 阳极氧化	钢, 铝	No
10713-111		24V min	1	镀锌铝, 阳极氧化	钢, 铝	No

物料号	交流输入电压	直流输入电压	包装数量	完成	材料	快速发货
10713-115		24V min	1	镀锌铝, 阳极氧化	钢, 铝	No
10713-110	115V		1	镀锌铝, 阳极氧化	钢, 铝	No

其他产品详情

请单独订购电源线。

可应要求提供广泛的输入电压范围 (86 ... 264 VAC)。

警告

应仅根据 nVent 的产品说明书与培训材料安装并使用 nVent 的产品。可访问 www.nvent.com 获取说明书，或者向您的 nVent 客服代表索取。错误安装、使用不当、滥用或未能完全遵守 nVent 的说明与警告，可能会造成产品故障、财产损失、严重的人身伤害及死亡和/或使得保修服务无效。

North America	Europe	Asia	Middle East & India
All locations +1.763.422.2661 Chat with us: nvent.com/schroff	Straubenhardt, Germany +49.7082.794.0 Betschdorf, France +33.3.88.90.64.90 Warsaw, Poland +48.22.209.98.35 Assago, Italy +39.02.932.7141 Chat with us: nvent.com/schroff	Shanghai, China +86.21.2412.6943 Qingdao, China +86.532.8771.6101 Singapore +65.6768.5800 Shin-Yokohama, Japan +81.45.476.0271 Chat with us: nvent.com/schroff	Dubai, United Arab Emirates +971.4.378.1700 Bangalore, India +91.80.6715.2001 Istanbul, Turkey +90.216.250.7374 Chat with us: nvent.com/schroff



我们强大的品牌组合:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE