

19" 风扇单元, 1 U, 速度控制和监测

风扇单元适合安装在机柜中的 1 U 空间内。



认证



功能

范围可选：20 ... 40 °C 和 30 ... 50 °C

降低温度相关的气流产生的噪声

外部传感器, 最大速度为默认故障状态

使用 LED 和干触点进行功能控制

符合 DIN EN ISO 13857 标准的接触保护

技术参数

Table 1/2

物料号	交流输入电压	直流输入电压	包装数量	完成	材料	认证
10713-098		24V min	1	镀锌铝, 阳极氧化	钢, 铝	CE, EAC, RoHS
19713-006	230V		1	镀锌铝, 阳极氧化	钢, 铝	CE, EAC, RoHS

物料号	交流输入电压	直流输入电压	包装数量	完成	材料	认证
10713-099		24V min	1	镀锌铝, 阳极氧化	钢, 铝	RoHS, CE, EAC
19713-121	230V		1	镀锌铝, 阳极氧化	钢, 铝	RoHS, EAC

Table 2/2	
物料号	快速发货
10713-098	No
19713-006	No
10713-099	No
19713-121	No

警告

应仅根据 nVent 的产品说明书与培训材料安装并使用 nVent 的产品。可访问 www.nvent.com 获取说明书，或者向您的 nVent 客服代表索取。错误安装、使用不当、滥用或未能完全遵守 nVent 的说明与警告，可能会造成产品故障、财产损失、严重的人身伤害及死亡和/或使得保修服务无效。

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab
Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



我们强大的品牌组合:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE