

19 英寸前面板, 塑料



19"

塑料前面板设计美观，专为数据通讯行业制造。易卡入安装面板有助于气流管理和提供更美观的机柜。

认证



功能

设计精美

通过卡入 19" 角轨简单装配

技术参数

附件类型: 前面板

Table 1/3

物料号	类型	安装	EMC 屏蔽	材料	正面表面处理	反面表面处理
87927-991	19" 前面板	卡扣嵌入式	否	ABS	未加工	未加工
87927-992	19" 前面板	卡扣嵌入式	否	ABS	未加工	未加工
23130-623	19" 前面板	卡扣嵌入式	否	ABS		

物料号	类型	安装	EMC 屏蔽	材料	正面表面处理	反面表面处理
23130-622	19" 前面板	卡扣嵌入式	否	ABS		

Table 2/3

物料号	颜色代码	机架高度	高度	机架宽度	宽度	深度
87927-991	RAL 7035	1U	43.71mm	95HP	482mm	12mm
87927-992	RAL 7035	2U	88.17mm	95HP	482mm	12mm
23130-623	RAL 7035	6U	266.6mm	95HP	483mm	2mm
23130-622	RAL 9005	6U	266.6mm	95HP	483mm	2mm

Table 3/3

物料号	包装数量	快速发货
87927-991	10	No
87927-992	10	No
23130-623	10	No
23130-622	10	No

警告

应仅根据 nVent 的产品说明书与培训材料安装并使用 nVent 的产品。可访问 www.nvent.com 获取说明书，或者向您的 nVent 客服代表索取。错误安装、使用不当、滥用或未能完全遵守 nVent 的说明与警告，可能会造成产品故障、财产损失、严重的人身伤害及死亡和/或使得保修服务无效。

North America

All locations

+1.763.422.2661

Chat with us:

nvent.com/schroff

Europe

Straubenhardt, Germany

+49.7082.794.0

Betschdorf, France

+33.3.88.90.64.90

Warsaw, Poland

+48.22.209.98.35

Assago, Italy

+39.02.932.7141

Chat with us:

nvent.com/schroff

Asia

Shanghai, China

+86.21.2412.6943

Qingdao, China

+86.532.8771.6101

Singapore

+65.6768.5800

Shin-Yokohama, Japan

+81.45.476.0271

Chat with us:

nvent.com/schroff

Middle East & India

Dubai, United Arab

Emirates

+971.4.378.1700

Bangalore, India

+91.80.6715.2001

Istanbul, Turkey

+90.216.250.7374

Chat with us:

nvent.com/schroff



我们强大的品牌组合:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE