

AC Fan

轴流式风扇，119 mm，带交流输入。适用于 1 U 风扇盘的替换部件。



认证



功能

带连接电缆插头的 119 mm 直流风扇

技术参数

Table 1/3

物料号	搭配	宽度	长度	高度	交流电压	频率
20713-147	19" 风扇盘	119mm	119mm	25mm	115V	50/60 Hz
20700-001	19" 风扇盘	119mm	119mm	25mm	230V	50/60 Hz
20713-142	19" 风扇盘	119mm	119mm	25mm	230V	50/60 Hz
20713-146	19" 风扇盘	119mm	119mm	25mm	115V	50/60 Hz

物料号	搭配	宽度	长度	高度	交流电压	频率
20713-243	19" 风扇盘	119mm	119mm	38mm	230V	50/60 Hz
20713-244	19" 风扇盘	119mm	119mm	38mm	115V	50/60 Hz

Table 2/3						
物料号	50 Hz 时的气流	60 Hz 时的气流	在 50 Hz 时的噪音等级	在 60 Hz 时的噪音等级	在 50 Hz 时的功率	在 60 Hz 时的功率
20713-147	108m³/h	120m³/h	34dB(A)	38dB(A)	14W	11W
20700-001	108m³/h	120m³/h	34dB(A)	38dB(A)	14W	11W
20713-142	84m³/h	90m³/h	29dB(A)	30dB(A)	8W	7W
20713-146	84m³/h	90m³/h	29dB(A)	30dB(A)	8W	7W
20713-243	162m³/h	192m³/h	37dB(A)	41dB(A)	15W	14W
20713-244	162m³/h	192m³/h	37dB(A)	41dB(A)	15W	14W

Table 3/3				
物料号	最大静压	环境温度	包装数量	快速发货
20713-147	41Pa	70°C	1	No
20700-001	41Pa	70°C	1	No
20713-142	23Pa	70°C	1	No
20713-146	23Pa	70°C	1	No
20713-243	73Pa	70°C	1	No
20713-244	73Pa	70°C	1	No

其他产品详情

请单独订购连接电缆和防护格栅。

警告

应仅根据 nVent 的产品说明书与培训材料安装并使用 nVent 的产品。可访问 www.nvent.com 获取说明书，或者向您的 nVent 客服代表索取。错误安装、使用不当、滥用或未能完全遵守 nVent 的说明与警告，可能会造成产品故障、财产损失、严重的人身伤害及死亡和/或使得保修服务无效。

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab
Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



我们强大的品牌组合:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE