

# CompacPRO 旋转把手

折叠式把手可用于搬运机箱或收起机箱



## 认证



## 功能

承载能力 20 千克

通过按钮以 30°为增量调整的把手

带粉末涂层的把手

对于桌面式应用，此把手有助于用户更方便地查看机箱正面

## 技术参数

搭配: 仪器箱  
产品系列: CompacPRO  
产品类型: 手柄

Table 1/1

| 物料号       | 机架宽度 | 包装数量 | 手柄类型  | 长度    | 材料     | 快速发货 |
|-----------|------|------|-------|-------|--------|------|
| 24575-038 | 42HP | 1    | 翻转式把手 | 180mm | 铝, 锌合金 | No   |

| 物料号       | 机架宽度 | 包装数量 | 手柄类型  | 长度    | 材料     | 快速发货 |
|-----------|------|------|-------|-------|--------|------|
| 24575-118 | 28HP | 1    | 翻转式把手 | 180mm | 铝, 锌合金 | No   |
| 24575-138 | 42HP | 1    | 翻转式把手 | 180mm | 铝, 锌合金 | No   |
| 24575-178 | 84HP | 1    | 翻转式把手 | 180mm | 铝, 锌合金 | No   |
| 24575-158 | 63HP | 1    | 翻转式把手 | 180mm | 铝, 锌合金 | No   |
| 24575-078 | 84HP | 1    | 翻转式把手 | 180mm | 铝, 锌合金 | No   |

警告

应仅根据 nVent 的产品说明书与培训材料安装并使用 nVent 的产品。可访问 [www.nvent.com](http://www.nvent.com) 获取说明书，或者向您的 nVent 客服代表索取。错误安装、使用不当、滥用或未能完全遵守 nVent 的说明与警告，可能会造成产品故障、财产损失、严重的人身伤害及死亡和/或使得保修服务无效。

North America

All locations  
+1.763.422.2661  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

Europe

Straubenhardt, Germany  
+49.7082.794.0  
Betschdorf, France  
+33.3.88.90.64.90  
Warsaw, Poland  
+48.22.209.98.35  
Assago, Italy  
+39.02.932.7141  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

Asia

Shanghai, China  
+86.21.2412.6943  
Qingdao, China  
+86.532.8771.6101  
Singapore  
+65.6768.5800  
Shin-Yokohama, Japan  
+81.45.476.0271  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

Middle East & India

Dubai, United Arab  
Emirates  
+971.4.378.1700  
Bangalore, India  
+91.80.6715.2001  
Istanbul, Turkey  
+90.216.250.7374  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)



我们强大的品牌组合:

CADDY   ERICO   HOFFMAN   ILSCO   SCHROFF   TRACHTE