

直流风扇

轴流风扇，119 mm，带直流输入。适用于 1 U 风扇盘的替换部件。



认证



功能

轴流 119 mm 直流风扇, 带连接电缆的插头

技术参数

Table 1/2						
物料号	搭配	宽度	长度	高度	直流电压	气流
20713-172	19" 风扇盘	119mm	119mm	25.5mm	24V	171m ³ /h
60713-600	19" 风扇盘	119mm	119mm	32mm	12V	140m ³ /h
20713-241	19" 风扇盘	119mm	119mm	38mm	12V	184m ³ /h
20713-242	19" 风扇盘	119mm	119mm	38mm	48V	184m ³ /h

物料号	搭配	宽度	长度	高度	直流电压	气流
20713-240	19" 风扇盘	119mm	119mm	38mm	24V	184m³/h

Table 2/2						
物料号	噪音等级	电源	最大静压	环境温度	包装数量	快速发货
20713-172	50.5dB(A)	7W	50.5Pa	70°C	1	No
60713-600	39dB(A)	8W	46Pa	70°C	1	No
20713-241	42dB(A)	8W	68Pa	70°C	1	No
20713-242	42dB(A)	8W	68Pa	70°C	1	No
20713-240	42dB(A)	8W	68Pa	70°C	1	No

其他产品详情

请单独订购连接电缆和防护格栅。

警告

应仅根据 nVent 的产品说明书与培训材料安装并使用 nVent 的产品。可访问 www.nvent.com 获取说明书，或者向您的 nVent 客服代表索取。错误安装、使用不当、滥用或未能完全遵守 nVent 的说明与警告，可能会造成产品故障、财产损失、严重的人身伤害及死亡和/或使得保修服务无效。

North America

All locations

+1.763.422.2661

Chat with us:

nvent.com/schroff

Europe

Straubenhardt, Germany

+49.7082.794.0

Betschdorf, France

+33.3.88.90.64.90

Warsaw, Poland

+48.22.209.98.35

Assago, Italy

+39.02.932.7141

Chat with us:

nvent.com/schroff

Asia

Shanghai, China

+86.21.2412.6943

Qingdao, China

+86.532.8771.6101

Singapore

+65.6768.5800

Shin-Yokohama, Japan

+81.45.476.0271

Chat with us:

nvent.com/schroff

Middle East & India

Dubai, United Arab

Emirates

+971.4.378.1700

Bangalore, India

+91.80.6715.2001

Istanbul, Turkey

+90.216.250.7374

Chat with us:

nvent.com/schroff



我们强大的品牌组合:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE