


车载机架 3 U, 84 HP

物料号

10170-014

适合持续振动、冲击、高温和高湿度环境。



认证



功能

适用于移动铁路应用

可用于持续振动, 冲击, 高温, 和高湿度环境

适用于 1, 2, 或 3 U SNCF 插箱 (NF F61-005, CF 60-002)

后侧配有标准连接器; 横杆可以针对 SNCF 编码销进行自定义编码

横杆带有集成电缆槽

多个机架可以彼此叠加或并排放置

使用焊接工艺生产, 获得 EN 15085 (CL2) 认证

不锈钢焊缝钝化, 防止腐蚀

产品属性

产品系列: 板载机架

机架高度: 3U
高度: 156.7mm
机架宽度: 84HP
宽度: 496.4mm
包装数量: 1
符合: SNCF NFF 61005; SNCF NFF 60002
深度: 341.8mm
框架材料: 钢
材料: 不锈钢
产品类型: 机架
静态负载: 25kg

警告

应仅根据 nVent 的产品说明书与培训材料安装并使用 nVent 的产品。可访问 www.nvent.com 获取说明书，或者向您的 nVent 客服代表索取。错误安装、使用不当、滥用或未能完全遵守 nVent 的说明与警告，可能会造成产品故障、财产损失、严重的人身伤害及死亡和/或使得保修服务无效。

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab
Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



我们强大的品牌组合:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE