

Varistar CP 车载机柜，机车车辆，铁路，38 U 1800 高 600 宽 400 深

物料号

10630-031



为了在移动环境中工作，电子系统的物理结构需要能够承受恶劣环境中的极端条件。

nVent SCHROFF cabinets are therefore designed to protect the electronics they house with high levels of mechanical stability and resistance to shock and vibration, according to EN 50155, , EN 45545, CENELEC and AREMA.

功能

EN 50155 抗冲击和振动认证

静态承载能力 1600 千克

防护类型 IP55

铁路认证焊接符合 EN 15085-2

产品属性

产品类型: 机柜

产品系列: Varistar CP

框架材料: 钢

机架高度: 38U

高度: 1800mm
宽度: 600mm
深度: 400mm
静态负载: 1600kg
防护等级: IP55
符合: EN 50155; IEC 60529; IEC 61587-1; IEC 60297-3-100; IEC 61587-2; EN 45545-2
颜色: 暗灰色
颜色代码: RAL 7021
完成: 粉末涂层
材料: 钢
Net Weight: 108kg
包装数量: 1
搭配: Varistar CP

警告

应仅根据 nVent 的产品说明书与培训材料安装并使用 nVent 的产品。可访问 www.nvent.com 获取说明书，或者向您的 nVent 客服代表索取。错误安装、使用不当、滥用或未能完全遵守 nVent 的说明与警告，可能会造成产品故障、财产损失、严重的人身伤害及死亡和/或使得保修服务无效。

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab
Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



我们强大的品牌组合:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE