

Varistar CP 抗震重型机柜，Bellcore Zone 4，EMC，2100 高 600 宽 600 深

物料号

10630-048



可以在“在线配置器”上配置其他尺寸和版本

Cabinet with IP 55 and EMC compliance for extreme seismic environments tested to Bellcore zone 4 with a dynamic load-carrying capacity of 500 kg. Customised solutions with higher loading are available. The cabinet is widely used in ICT applications in earthquake prone areas, Construction and Shipping Facilities, Airports, Railways and many more.

功能

抗震安全等级高达 Bellcore Zone 4, 已根据 Telcordia GR-63 Core 使用 500 千克进行测试, NEBS 认证

静态承载能力 1600 千克

防护类型 IP55

已根据 IEC 61587 - 3 进行高屏蔽能力测试, 带 EN45545-2 防火安全垫片

产品属性

产品类型: 机柜

产品系列: Varistar CP

框架材料: 钢

完成: 粉末涂层

机架高度: 42U
高度: 2000mm
宽度: 600mm
深度: 600mm
静态负载: 1600kg
防护等级: IP55
符合: IEC 60529; IEC 61587-1; IEC 60297-3-100; IEC 61587-3; IEC 61587-1; IEC 61587-2; EN 45545-2; Telcordia GR-63
核心区域 4
颜色: 暗灰色
颜色代码: RAL 7021
频率: 50 Hz
材料: 钢
Net Weight: 180.164kg
包装数量: 1
耐冲击和振动性: 5g (force)
搭配: Varistar CP

警告

应仅根据 nVent 的产品说明书与培训材料安装并使用 nVent 的产品。可访问 www.nvent.com 获取说明书，或者向您的 nVent 客服代表索取。错误安装、使用不当、滥用或未能完全遵守 nVent

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab
Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



我们强大的品牌组合:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE