

Varistar CP MIL 901E

机柜，经军用认证的抗冲击、抗震动、抗 EMC 和抗腐蚀性

物料号

10630-049



Cabinet with military certification for battle readiness and surviving harsh environments. The enclosures are for frigate, airforce and military applications.

Globally military organizations maintains a comprehensive list of standards for equipment deployed in military applications. By selecting equipment qualified to these standards, design engineers can ensure COTS solutions already meet the minimum requirements to protect mission critical systems.

功能

经 NTS 测试，根据 MIL-DTL-901E 执行 DSSM 跌落台测试，负载重量为 460 千克

经 NTS 测试，根据 TP-PR168728-00 执行 EMI 屏蔽测试程序 - 符合 MIL-STD-461G

经 NTS 测试，根据 Mil-STD-810H 执行耐腐蚀性测试

经 NTS 测试，根据 Mil-STD- 167-1A 执行振动测试

双重防腐蚀, 镀锌和粉末涂层

底部有 4 个减震器, 顶部有 2 个减震器

后面板水平分为 3 部分 - 顶部盖板覆盖减震器固定区域, 电缆管道底部盖板, 中部后面板封闭盖板之间的间隙

EMC 底板配有通孔, 可将减震器直接连接至框架

产品属性

产品类型: 机柜

产品系列: Varistar CP

框架材料: 钢

框架颜色: 暗灰色

框架颜色代码: RAL 7021

覆层材料: 钢

覆层颜色: 暗灰色

覆层颜色代码: RAL 7021

机架高度: 42U

高度: 2000mm

宽度: 600mm

深度: 800mm

静态负载: 1600kg

动态荷载: 460kgf

防护等级: IP55

符合: IEC 60529; MIL-S-901E; MIL-STD-461G; MIL-STD-810E; MIL-STD-167

完成: 粉末涂层

材料: 钢; Stainless 钢

包装数量: 1

警告

应仅根据 nVent 的产品说明书与培训材料安装并使用 nVent 的产品。可访问 www.nvent.com 获取说明书, 或者向您的 nVent 客服代表索取。错误安装、使用不当、滥用或未能完全遵守 nVent 的说明与警告, 可能会造成产品故障、财产损失、严重的人身伤害及死亡和/或使得保修服务无效。

North America

All locations

+1.763.422.2661

Chat with us:

nvent.com/schroff

Europe

Straubenhardt, Germany

+49.7082.794.0

Betschdorf, France

+33.3.88.90.64.90

Warsaw, Poland

+48.22.209.98.35

Assago, Italy

+39.02.932.7141

Chat with us:

nvent.com/schroff

Asia

Shanghai, China

+86.21.2412.6943

Qingdao, China

+86.532.8771.6101

Singapore

+65.6768.5800

Shin-Yokohama, Japan

+81.45.476.0271

Chat with us:

nvent.com/schroff

Middle East & India

Dubai, United Arab

Emirates

+971.4.378.1700

Bangalore, India

+91.80.6715.2001

Istanbul, Turkey

+90.216.250.7374

Chat with us:

nvent.com/schroff



我们强大的品牌组合:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE