

Varistar CP 抗震机柜, bellcore zone 4, EMC, 2100H 600W 600D

物料号

10630-050



功能

抗震安全等级高达 Bellcore Zone 4, 已根据 Telcordia GR-63 Core 使用 250 千克进行测试

静态承载能力 1600 千克

防护类型 IP55

已根据 IEC 61587 - 3 进行高屏蔽能力测试, 带 EN45545-2 防火安全垫片

产品属性

产品类型: 机柜

产品系列: Varistar CP

框架材料: 钢

机架高度: 42U

高度: 2000mm

宽度: 600mm

深度: 600mm

静态负载: 1600kg
防护等级: IP55
符合: IEC 60529; IEC 61587-1; IEC 60297-3-100; IEC 61587-3; IEC 61587-1; IEC 61587-2; EN 45545-2; Telcordia GR-63
核心区域 4
颜色: 暗灰色
颜色代码: RAL 7021
完成: 粉末涂层
频率: 50 Hz
材料: 钢
包装数量: 1
耐冲击和振动性: 5g (force)
搭配: Varistar CP

警告

应仅根据 nVent 的产品说明书与培训材料安装并使用 nVent 的产品。可访问 www.nvent.com 获取说明书，或者向您的 nVent 客服代表索取。错误安装、使用不当、滥用或未能完全遵守 nVent 的说明与警告，可能会造成产品故障、财产损失、严重的人身伤害及死亡和/或使得保修服务无效。

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab
Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



我们强大的品牌组合:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE