


19" 推送式风扇盘，2 U，轴向，230 VAC，板深度 220mm，445 - 530 M³h

物料号

10713-526



带集成推送式风扇的风扇托盘。

认证



功能

符合 DIN EN ISO 13857 标准的接触保护

集成式空气导流板可防止安装在下方的组件积聚热量

可根据插箱规格进行调整

可选择加装后部风扇, 2 U, 用于为推送式风扇下方的组件进行主动冷却

产品属性

产品类型: 风扇单元
交流输入电压: 230V
包装数量: 1
完成: 镀锌铝
材料: 钢; 聚丙烯

其他产品详情

请单独订购电源线。

警告

应仅根据 nVent 的产品说明书与培训材料安装并使用 nVent 的产品。可访问 www.nvent.com 获取说明书，或者向您的 nVent 客服代表索取。错误安装、使用不当、滥用或未能完全遵守 nVent 的说明与警告，可能会造成产品故障、财产损失、严重的人身伤害及死亡和/或使得保修服务无效。

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab
Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



我们强大的品牌组合:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE