

19 英寸风扇单元，1 U，远程控制和监控，6 风扇，100-240 VAC

物料号

10713-554



带 ModBus 接口的风扇单元适合安装在机柜的 1 U 空间内

认证



功能

支持风扇速度温度监控

适用于远程监控和控制的 ModBus 接口

前面板上的风扇控制装置可调节温度阈值

通过 2 个 LED 灯和无电势继电器输出风扇故障和超温信号

支持宽幅电压输入 (100 V – 240 V) 的集成电源

不到 1 U (42 mm)，可安装在滑动导轨或抽屉上

2 NTC 温度传感器，含电缆

产品属性

产品类型: 风扇单元
交流输入电压: 100 – 240V
气流: 1089m³/h
噪音等级: 59.5dB(A)
电源: 97W
最大静压: 78Pa
环境温度: -10 to 70°C
使用寿命, 在 40 C 时 L10: 99558h
包装数量: 1
完成: 镀锌铝; 阳极氧化
Gross Weight: 5.2kg
材料: 钢; 铝

警告

应仅根据 nVent 的产品说明书与培训材料安装并使用 nVent 的产品。可访问 www.nvent.com 获取说明书, 或者向您的 nVent 客服代表索取。错误安装、使用不当、滥用或未能完全遵守 nVent 的说明与警告, 可能会造成产品故障、财产损失、严重的人身伤害及死亡和/或使得保修服务无效。

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab
Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



我们强大的品牌组合:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE